

## M23\_19P FE,Int-thread,ANG PUR cable,5M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 360 0D74 050
Specification	M23_19P FE,Int-thread,ANG PUR cable,5M
HARTING eCatalogue	<a href="https://harting.com/21373600D74050">https://harting.com/21373600D74050</a>

### Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Female Angled
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant Halogen freeness

### Version

Cable length	5 m
Number of cores	19
Core structure	3x AWG 18 + 16x AWG 22

### Technical characteristics

Rated voltage	150 V
Rated current (signal)	2 A
Rated current (power)	9 A
Limiting temperature	-40 ... +80 °C



Pushing Performance  
Since 1945

## Technical characteristics

Degree of protection acc. to IEC 60529	IP67
--	------

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (cable)	PUR (polyurethane)
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Net weight	968 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140241305
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604