

PLC-APT-PT100-IN - Analog module



2906919

<https://www.phoenixcontact.com/us/products/2906919>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pt 100/Pt 1000 temperature transducer for PLC logic logic modules (Generation 2 only), single-channel, signal type (Pt 100, Pt 1000) can be configured via DIP switch, Push-in connection

Commercial data

Item number	2906919
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C424
Product key	DK2622
Catalog page	Page 433 (C-5-2019)
GTIN	4055626155500
Weight per piece (including packing)	73 g
Weight per piece (excluding packing)	50.3 g
Customs tariff number	85389099
Country of origin	DE

PLC-APT-PT100-IN - Analog module



2906919

<https://www.phoenixcontact.com/us/products/2906919>

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Product properties

Product type	Extension module
Product family	PLC logic
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV

Supply

Rated control circuit supply voltage U_S	24 V DC
Rated control supply voltage range with reference to U_S	0.8 ... 1.1
Rated control supply current I_S	14 mA
Protective circuit	Reverse polarity protection
	Surge protection

Input data

Analog input resistance

Sensor types (RTD) that can be used	Pt 100 (IEC 60751, $\alpha = 0.00385$)
Number of inputs	1
Connection technology	2-conductor
Sensor input current	900 μ A
Temperature measuring range	-50 °C ... 200 °C
Maximum temperature coefficient	0.01 %/K
Maximum transmission error	1 %
Surge voltage protection	> 33 V
Resolution	10 bit (scaled to 0 to 1000)

Analog input resistance

Sensor types (RTD) that can be used	Pt 1000 (IEC 60751, $\alpha = 0.00385$)
-------------------------------------	--

PLC-APT-PT100-IN - Analog module



2906919

<https://www.phoenixcontact.com/us/products/2906919>

Number of inputs	1
Connection technology	2-conductor
Sensor input current	900 µA
Temperature measuring range	-50 °C ... 200 °C
Maximum temperature coefficient	0.01 %/K
Maximum transmission error	1 %
Surge voltage protection	> 33 V
Resolution	10 bit (scaled to 0 to 1000)

Output data

Digital

Output name	Digital output
Switching voltage range	5 V DC ... 30 V DC
Switching current	≤ 3 mA

Connection data

Connection method	Push-in connection
Stripping length	10 mm
Number of connections	4
Conductor cross section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Signaling

Operating voltage display	Green LED
Error indication	Red LED

Dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Approvals

CE

PLC-APT-PT100-IN - Analog module

2906919

<https://www.phoenixcontact.com/us/products/2906919>



Certificate	CE-compliant
UL, USA/Canada	
Identification	UL 508 Listed

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any


PLC-APT-PT100-IN - Analog module



2906919

<https://www.phoenixcontact.com/us/products/2906919>

Drawings



PLC-APT-PT100-IN - Analog module

2906919

<https://www.phoenixcontact.com/us/products/2906919>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906919>



EAC

Approval ID: RU*DE.*08.B.01517/19



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

PLC-APT-PT100-IN - Analog module

2906919

<https://www.phoenixcontact.com/us/products/2906919>



Classifications

ECLASS

ECLASS-13.0	27242201
-------------	----------

ETIM

ETIM 9.0	EC001420
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

PLC-APT-PT100-IN - Analog module

2906919

<https://www.phoenixcontact.com/us/products/2906919>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9b8eefa1-17ef-4128-be9a-cd6923b16263

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com