

## M12 D-cod 4-pol st/st m/m PUR PP 10.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 404 0445 100
Specification	M12 D-cod 4-pol st/st m/m PUR PP 10.0m
HARTING eCatalogue	<a href="https://harting.com/21404040445100">https://harting.com/21404040445100</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Locking type	PushPull

### Technical characteristics

Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz

## Technical characteristics

Limiting temperature	-40 ... +70 °C moved -20 ... +60 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	6.5 mm ± 0.2 mm
Minimum bending radius	3x Cable diameter (singular bending) 7x Cable diameter (repeated bending)
Bending cycles	≥ 3.000.000 & 7x Cable diameter & traversing distance ≤ 0.2 m & speed ≤ 4 m/s & acceleration ≤ 4 m/s <sup>2</sup>

## Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	UN/ECE-R 118
----------------	--------------

## Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140489998
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599

## Commercial data

UNSPSC 24.0

26121600