

M12 X-cod 8-pol an/- m/- RAIL PP 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 620 0888 015
Specification	M12 X-cod 8-pol an/- m/- RAIL PP 1.5m
HARTING eCatalogue	https://harting.com/21406200888015

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 X-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	8
Core structure	4x 2x AWG 24/7
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Locking type	PushPull

Technical characteristics

Rated current	0.5 A
Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Limiting temperature	-40 ... +80 °C moved -25 ... +70 °C unmoved



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	8.1 mm ± 0.3 mm
Minimum bending radius	5x Cable diameter (singular bending)
	6x Cable diameter (repeated bending)

Material properties

Material (cable)	Polyolefin copolymer
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
	Triphenyl phosphate
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	UN/ECE-R 118
	EN 45545

Commercial data

Packaging size	1
Net weight	123 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140342415
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600