

## Ha-VIS eCon 3060B-A



Image is for illustration purposes only. Please refer to product description.

Part number	24 03 006 0010
Specification	Ha-VIS eCon 3060B-A
HARTING eCatalogue	<a href="https://harting.com/24030060010">https://harting.com/24030060010</a>

### Identification

Series	Ha-VIS eCon 3000
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Fast Ethernet

### Version

Total number of ports	6
Fixing	35 mm DIN rail acc. to EN 60715
Switching technology	Store and Forward
Frame size	1.522 kB
MAC table size	1k Entries
Packet buffer size	0.44 Megabit
Non blocking	Yes
Quality of service	Yes
Energie Efficient Ethernet	Yes
Flow control	Off
Signal contact	No
PoE functionality	No
Pack contents	Pluggable screw contact for power supply Assembly instructions

### Termination data

Nominal voltage	24 V DC 48 V DC
-----------------	--------------------



**Pushing Performance**  
 Since 1945

## Termination data

Permissible voltage	9 ... 60 V DC
Surge protection	Yes
Operating current	<75 mA @ 24 V DC <40 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	<1.6 A @ 24 V DC <3.2 A @ 48 V DC
Overcurrent protection	12 A at input
Power consumption	<1.8 W @ 24 V DC
Termination method	Pluggable screw contact
Number of contacts	3
Conductor cross-section	0.08 ... 2.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 28 ... AWG 12
Pinout	+ / - / FE
Reverse polarity protection	Yes

## Technical characteristics

Operating temperature	0 ... +55 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition
MTBF	≈2,290,000 h

## Ethernet ports copper

10/100 Mbit/s (RJ45-Ports)	6
Transmission standard	10BASE-Te 100BASE-TX EEE
Auto-negotiation	Yes
Auto-polarity	Yes
Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s 100 Mbit/s



**Pushing Performance**  
 Since 1945

## Ethernet ports copper

Transmission length 100 m

## Material properties

Material (hood/housing)	Aluminium (anodised) Steel sheet (powder-coated)
Length	107.5 mm
Width	25 mm
Height	142 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	EN 55022 Radio disturbance characteristics EN 61000-4-2 Electrostatic discharge (ESD) EN 61000-4-3 Electromagnetic field EN 61000-4-4 Rapid transients (burst) EN 61000-4-5 Surge voltages EN 61000-4-6 conducted disturbances EN 61000-6-4 emission standard IEC 60068-2-6 Vibration (sinusoidal)
UL / CSA	UL 508 NRAQ.E253944 CSA-C22.2 No. 142 NRAQ7.E253944
Approvals	CE DNV GL
FCC	Yes

## Commercial data

Packaging size	1
Net weight	574 g
Country of origin	Germany
European customs tariff number	85176200



**Pushing Performance**  
Since 1945

## Commercial data

GTIN	5713140147966
eCl@ss	19170130 Network switch (general application)
ETIM	EC000734
UNSPSC 24.0	43222612