

## FO-BH-D 2Ch 50/125 OM3 - LCdx, 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 04 411 0010 001
Specification	FO-BH-D 2Ch 50/125 OM3 - LCdx, 1,0m
HARTING eCatalogue	<a href="https://harting.com/33044110010001">https://harting.com/33044110010001</a>

### Identification

Category	System cabling
Series	Expanded beam
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Expanded beam 2 channels
Connector 2	LC duplex
Type of cable	FO cable
Description of the cable	Multimode

### Version

Cable length	1 m
Number of fibres	2
Fiber type	2G50/125 OM3

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP68
Cable diameter	3 mm

### Material properties

Material (hood/housing)	Aluminium
Colour (hood/housing)	Black
RoHS	compliant

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	8a5c37c3-d5dc-469f-b994-a066c654819f
California Proposition 65 substances	Not contained

## Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Latvia
European customs tariff number	85447000
GTIN	5713140271012
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600