

MPP ix Type A - RJ45 IP20 Cat6A PUR 1,0m




Image is for illustration purposes only. Please refer to product description.

Part number	33 48 344 7804 010
Specification	MPP ix Type A - RJ45 IP20 Cat6A PUR 1,0m
HARTING eCatalogue	https://harting.com/33483447804010

Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	 HARTING Mini PushPull HARTING ix Industrial® Type A Overmoulded IDC termination
Connector 2	HARTING DualBoot RJ45 Piercing termination
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC insulation displacement termination Piercing termination

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
------------------------------	--

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C
Cable diameter	6.7 mm ± 0.3 mm

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	UN/ECE-R 118
	IEC 60332-1-2 Flame retardancy
	UL 1581, Sec. 1090 (H) Flame retardancy
	EN 60811-404 Oil resistance
	UL style 21815
	IEC 60754-2 Halogen freeness
	EN 50618 UV resistant

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140796805
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600