

Han F+B CA 17D 0,5mm² m/- st/- PUR 5,0m



Part number	33 50 410 0306 050
Specification	Han F+B CA 17D 0,5mm ² m/- st/- PUR 5,0m
HARTING eCatalogue	https://harting.com/33504100306050

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Series	Han® F+B
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Male Hood
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	17
Core structure	0.5 mm ²
Number of contacts	17
PE contact	Yes

Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-20 ... +80 °C moved -40 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP69

Technical characteristics

Minimum bending radius	10x Cable diameter (repeated bending) 5x Cable diameter (singular bending)
------------------------	---

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Grey

Specifications and approvals

Specifications	EN 50525-1 IEC 60228 EN 50363-3 EN 50363-10-2
Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topactive OKTO Ecolab Topax 66 Ecolab Topax 990

Commercial data

Packaging size	1
Net weight	1,200 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140238176
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604