

Hybr.cable Assy,AC,5m,FO+POW-MM-2xHAN3A



Image is for illustration purposes only. Please refer to product description.

Part number	33 57 211 0055 001
Specification	Hybr.cable Assy,AC,5m,FO+POW-MM-2xHAN3A
HARTING eCatalogue	https://harting.com/33572110055001

Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Han® 3 A Metal LC duplex
Connector 2	Han® 3 A Metal LC duplex
Type of cable	Hybrid cable (copper/FO)
Description of the cable	Multimode AC version

Version

Cable length	5 m
Core structure	2x G50 / 125 µm 3x 2.5 mm ²

Technical characteristics

Cable diameter	12.6 mm
----------------	---------

Material properties

Material (cable)	PVC
RoHS	compliant with exemption
RoHS exemptions	6(b)-III: Lead as an alloying element in aluminium casting alloys containing up to 0,3 % lead by weight provided it stems from lead-bearing aluminium scrap recycling 6(c): Copper alloy containing up to 4 % lead by weight



Pushing Performance
Since 1945

Material properties

ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	1,466 g
Country of origin	Czechia
European customs tariff number	85447000
GTIN	5713140151642
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600