

HYBRID CABLE 2xFO MM,10M,RING



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|--------------------------|--------------------------|
| Category | System cabling |
| Element | Bulk cables |
| Specification | Not assembled |
| Type of cable | Hybrid cable (copper/FO) |
| Description of the cable | Multimode |

Version

| | |
|----------------|--|
| Cable length | 10 m |
| Core structure | 2x G50 / 125 μ m 3x 2.5 mm ² |

Technical characteristics

| | |
|------------------------|---|
| Cable diameter | 12.6 mm |
| Minimum bending radius | 10x Cable diameter (repeated bending) 5x Cable diameter (singular bending) |

Material properties

| | |
|-----------------------------|--|
| Material (cable) | PVC |
| Colour (cable) | Black |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |

Material properties

| | |
|--------------------------------------|---------------|
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |

Commercial data

| | |
|--------------------------------|-----------------------|
| Packaging size | 1 |
| Net weight | 2,200 g |
| Net weight | 217 g/m |
| Country of origin | Germany |
| European customs tariff number | 85444290 |
| GTIN | 5713140274020 |
| eCl@ss | 27060501 Hybrid cable |
| ETIM | EC001579 |
| UNSPSC 24.0 | 26121639 |