Pushing Performance
Since 1945

Han-Mod_M_Carrier_C.2_Long




Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 0430
Specification	Han-Mod_M_Carrier_C.2_Long
HARTING eCatalogue	https://harting.com/97000000430

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Carrier Cube
Size of the module	Domino module
Description of the module	Long version Large Tab

Version

Details	Insulated to the hinged frame.

Technical characteristics

Limiting temperature	-40 ... +85 °C

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com