



Pushing Performance
Since 1945

Han-Mod_M_70A_2_M_S_CRT_CAV NO 3 + N




Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 2158
Specification	Han-Mod_M_70A_2_M_S_CRT_CAV NO 3 + N
HARTING eCatalogue	https://harting.com/97000002158

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® 70 A module
Size of the module	Single module

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	2
Contact identification	3 N
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section (mm²)	6 ... 25 mm²
Wire outer diameter	≤11.5 mm
Rated current	70 A
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥10,000



Pushing Performance
Since 1945

Technical characteristics

Note on the mating cycles

Mating cycles with other HMC components

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	4 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)
ETIM	EC000438
UNSPSC 24.0	39121552