


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	WEIGHT lbs/100pcs (g)
	MIN in (mm)	MAX in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	90 (400.3)	EXTRA HEAVY	1.3 (590)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	90 (400.3)	EXTRA HEAVY	2.5 (1134)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	90 (400.3)	EXTRA HEAVY	2.8 (1270)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	90 (400.3)	EXTRA HEAVY	3.8 (1724)

* SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR

						TITLE		PREMIUM RELEASABLE LASHING TIES - POLYPROPYLENE	
						CUSTOMER DRAWING			
						ITEM REVISION NAME		W10001BH/08	
						DATASET FILE NAME		W10001BH_DC/08	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
						.x ± .1 [2.5] .xxx ± .010 [.25] .xx ± .02 [.5] ANGLES ±		POLYPROPYLENE	
						THIRD ANGLE PROJECTION		DRAWING NUMBER:	
						SS-15129		SS-15129	
08A	9.12.24	BWG	JADE	DJSL	UPDATED TITLE BLOCK WITH ALTERNATE DESCRIPTION	005806/00			
7	11.18.14	BDK	MPH	JADE	UPDATED TITLE BORDER	SS-15129			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK
							DWR	7-15-77	HVP
							SCALE	NONE	SHT 1 OF 1
							SIZE	A	