

# IndustrialNet™ Variant 1 Bulkhead Connectors

**PANDUIT®**  
SPECIFICATION SHEET

## SPECIFICATIONS

8-position, industrial connector shall be applicable for use in manufacturing environments and shall meet/exceed the ANSI/TIA-568.2-D standards for Category performance requirements. Bulkhead RJ45 jack and plug shall incorporate an IP67 rated seal and shall be designed to provide protection from dust and temporary immersion in water typically found in harsh industrial environments. Tethered protective cap shall ensure IP67 protection of the connector and plug in the unmated condition. Secondary seals on both the connector and plug shall provide an additional environmental barrier. Termination to a 4-pair 24 AWG, 100 ohm twisted pair cable shall not require the use of a punch down tool. An IP67 rating shall be achieved when mated with an IP67 and NEMA UL Type 12, 6/6P, 4X industrial grade, bayonet style patch cord.



## TECHNICAL INFORMATION

<b>Channel and component performance:</b>	Exceeds channel and component requirements of ANSI/TIA-568.2-D Category and ISO11801 Class E standards at swept frequencies for each performance category
<b>Electrical/mechanical performance:</b>	Meets all ODVA Ethernet/IP <sup>^</sup> electrical and mechanical performance requirements
<b>Environmental protection:</b>	Protects and seals connections against dust and water immersion to ANSI/IEC 60529-2004 Vibration, temperature and chemical resistant; shielded version further enhances electromagnetic performance
<b>FCC and ANSI/TIA compliance:</b>	Meets ANSI/TIA-1096-A; contacts plated with 50 micro inches of gold for superior performance
<b>IEC compliance:</b>	Plug meets IEC 60603-7 specifications
<b>IP compliance:</b>	Rated IP67 for dust protection and temporary liquid immersion
<b>NEMA/UL compliance:</b>	Rated UL Type 12, 6/6P, 4X
<b>Material:</b>	Bulkhead connector is constructed of black PBT plastic
<b>Packaging:</b>	Connector and plug include protective cap
<b>RoHS compliance status:</b>	Compliant
<b>PoE compliance:</b>	Meets IEEE 802.3af and IEEE 802.3at for PoE applications

## KEY FEATURES AND BENEFITS

<b>IP/NEMA/UL rated connection:</b>	Withstands light wash down and temporary submerged conditions in harsh factory environments without loss of performance when mated to IP67 IndustrialNet Patch Cords; Maintains NEMA 4/4X rating when properly installed on NEMA 4/4X enclosures
<b>Bayonet style interface:</b>	Provides positive reinforcement during mated condition; rated to 100 mating cycle
<b>Protective cap:</b>	Maintains IP67 seal during unmated connection
<b>Industry standard RJ45 interface:</b>	Offers industry standard solution familiar to end users which speeds deployment
<b>No punchdown tool required:</b>	Can terminate with standard adjustable slipjaw pliers or optional termination tool (EGJT)
<b>Standard mounting:</b>	Bulkhead connector fits into standard IEC 1-13/64" (30.5mm) diameter mounting hole or optional faceplate

### IndustrialNet TX6A™ Connectors

<b>UTP:</b>	IAEBH6X
<b>STP:</b>	IAEBH6XS
<b>Coupler, Shielded:</b>	IAEBHC6XS

### IndustrialNet TX6™ PLUS Connectors

<b>UTP:</b>	IAEBH6
<b>STP:</b>	IAEBH6S
<b>Coupler, Unshielded:</b>	IAEBHC6

### IndustrialNet TX5e™ Connectors

<b>Unshielded:</b>	IAEBH5E
<b>Shielded:</b>	IAEBH5ES
<b>Coupler, Unshielded:</b>	IAEBHC5E
<b>Coupler, Shielded:</b>	IAEBHC5ES

### IndustrialNet TX5e™ Modular Plugs

<b>UTP:</b>	MPI588T
<b>Shielded:</b>	MPSI588T

### IndustrialNet USB Coupler

<b>Female A to female A:</b>	IAEBHUSBAA
------------------------------	------------

### IndustrialNet TX6A™ Patch Cords

<b>UTP with bulkhead connector on both ends:</b>	IUTP6X*MBL
--------------------------------------------------	------------

<b>STP with bulkhead connector on both ends:</b>	ISTP6X*MBL
--------------------------------------------------	------------

<b>STP with bulkhead connector on one end:</b>	ISTP6X*MBLR
------------------------------------------------	-------------

### IndustrialNet TX6™ Patch Cords

<b>STP with caps:</b>	ISTPSP**MBL
-----------------------	-------------

### IndustrialNet TX5e™ Patch Cords

<b>UTP with caps:</b>	IUTPCH***BLY
-----------------------	--------------

<b>STP with caps:</b>	ISTPCH***1MBLY
-----------------------	----------------

### IndustrialNet Stainless Steel Faceplates

<b>Single gang:</b>	IAEFP1
---------------------	--------

<b>Double gang:</b>	IAEFP2-2G
---------------------	-----------

### Tools and Accessories

<b>Termination tool (optional):</b>	EGJT-1 and TGJT
-------------------------------------	-----------------

<b>Wire snipping tool:</b>	CWST
----------------------------	------

<b>Wire stripping tool:</b>	CJAST
-----------------------------	-------

<sup>\*</sup>Meter lengths: 2, 3, 5, or 10 meters

<sup>\*\*</sup>Feet lengths: 5, 7, 10, 15, or 20 feet

<sup>\*\*\*</sup>Meter lengths: 2, 3, or 5 meters

<sup>^</sup>EtherNet/IP is a trademark of ODVA.





All listed part numbers are compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to customers in the United States.

# IndustrialNet™ Variant 1 Bulkhead Connectors


## APPLICATIONS

IndustrialNet Variant 1 Bulkhead Connectors provide an ideal solution to support industrial Ethernet from the Local Area Network (LAN) based support offices to the processing devices on the plant floor even under harsh industrial conditions. Innovative design features provide a secure, reliable connection for superior data transmission in work cells where moisture and dust/particles are encountered, in temperature extremes and in applications with vibration. Industrial bulkhead connection protects and seals against dust and water immersion common in the food and beverage industry where bacterial contamination is present and light wash down is required. High temperature resilience of up to 85°C storage and 75°C operating offers reliable connection in manufacturing facilities such as metal processing, welding, and chemical batch processing where high temperatures are normal. In automotive panel stamping plants and work cells where vibration is a concern, the IndustrialNet Connectors protect the RJ45 mating.

## ENGINEERING DRAWINGS



# IndustrialNet™ Variant 1 Bulkhead Connectors



---

## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
COSP476-WW-ENG  
7/2024

**PANDUIT®**