

TX6-ER U/UTP 22 AWG Outside Plant (OSP) Copper Cable

North America

PANDUIT
SPECIFICATION SHEET

SPECIFICATIONS

Category 6 OSP cable shall meet the ANSI/TIA-568.2-D Category 6 component standard. The conductors shall be 22 AWG construction with polyolefin insulation. The cable shall have a gel-filled construction to prevent moisture migration in wet applications and a wide temperature range for extreme weather environments. The copper conductors shall be twisted in pairs, separated by a pair separator and covered with a UV- and abrasion-resistant polyethylene (PE) jacket. Product is to be used in duct and conduit installations only. Not to be used in aerial or direct burial applications. Provides less voltage drop, increased current carrying capacity and reduced heat generation for PoE applications. Exceeds the 100 meter distance for security, ICT, building automation, and IoT applications.



TX6-ER U/UTP 22 AWG Copper Cable

OSP:

PUO6C2204BL-GZ

TECHNICAL INFORMATION

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds ANSI/TIA-568.2-D Category 6 standard at swept frequencies up to 250 MHz.
	Certified component performance up to 100 meters and exceeds the component requirements of ANSI/TIA-568.2-D Category 6 component standard at swept frequencies up to 250 MHz.
Conductors/insulators:	22 AWG solid copper insulated with polyolefin
Insulation diameter:	0.048 in. – 0.053 in. (1.22mm – 1.35mm)
Standards compliance:	ANSI/TIA-568.2-D Category 6, Telcordia (Bellcore) Specification GR-421-CORE Water Penetration Requirement
Installation tension:	25 lbf (110 N) maximum
Temperature rating:	-22°F to 140°F (-30°C to 60°C) during installation -49°F to 176°F (-45°C to 80°C) during operation
Cable jacket:	Black UV-resistant and abrasion-resistant polyethylene (PE)
Cable diameter:	0.291 in. (7.4mm) nominal
Cable weight:	40 lbs./1000 ft. (19 kg/305m)
Packaging:	1000 ft. (305m) on a reel Package tested to ISTA Procedure 1A

KEY FEATURES AND BENEFITS

Longer runs for labor and material savings:	Provides power and bandwidth at extended distances of 150 meters based on the IEEE 802.3 application standards. Maximum distance is subject to change based on manufacturer's equipment and varying environmental conditions.
High powered applications:	Larger AWG conductors for higher power applications (reduced heat generation, higher maximum current carrying capabilities, improved attenuation).
Robust design:	Protects against environmental elements that can cause electrical performance failures. Wide temperature range for extreme weather environments.
Flooding compound:	Waterproof gel prevents moisture migration
Reel:	Ensures proper performance and provides quick installation
Descending length cable markings:	Easy identification of remaining cable reduces installation time and cable scrap

APPLICATIONS

TX6-ER U/UTP OSP Copper Cable is a component of the TX6 U/UTP Copper Cabling System. This end-to-end system provides Gigabit Ethernet performance with usable bandwidth beyond 250 MHz. With certified performance to the ANSI/TIA-568.2-D Category 6 Standard, this system will support the following applications:

- Ethernet 10BASE-T
- 100BASE-T (Fast Ethernet)
- 1000BASE-T (Gigabit Ethernet)




All listed part numbers are compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to customers in the United States.

TX6-ER U/UTP 22 AWG Outside Plant (OSP) Copper Cable

ADDITIONAL SPECIFICATIONS

Mechanical Testing	
Ultimate breaking strength:	> 400 N (90 lbf)
Minimum bend radius:	4 x cable diameter
Engineering Testing	
Nominal velocity of propagation (NVP):	66% nominal
Operating voltage, maximum:	80 V

ENGINEERING DRAWINGS



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT[®]

© 2024 Panduit Corp.
ALL RIGHTS RESERVED.
COSP627-WW-ENG
9/2024