

UC-EMLP (22X22) SR CUS - Plastic label

0826987

<https://www.phoenixcontact.com/us/products/0826987>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, can be ordered: by sheet, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 6, text field height: 22 mm, text field width: 22 mm



Your advantages

- All UC-EMLP ... self-adhesive device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0826987
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8147
Catalog page	Page 235 (C-5-2013)
GTIN	4046356448109
Weight per piece (including packing)	10.1 g
Weight per piece (excluding packing)	7.3 g
Country of origin	PL

UC-EMLP (22X22) SR CUS - Plastic label

0826987

<https://www.phoenixcontact.com/us/products/0826987>



Technical data

Product properties

Product type	Labeled device marker
Marking	
Number of individual labels	6
Number of individual labels per row	2
Identification technology	UV LED technology

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Test for substances that would hinder coating with paint or varnish	

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Mounting

Mounting type	adhesive
Mounting	

Material specifications

RoHS compliant	yes
Adhesive strength	250 µm
Adhesive	Acrylic
Color	silver-colored
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

UC-EMLP (22X22) SR CUS - Plastic label

0826987

<https://www.phoenixcontact.com/us/products/0826987>



Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	22 mm
Length	22 mm

Text field

Text field width	22 mm
Text field height	22 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
<hr/>	
Standards	

Standards/regulations

EN 45545-2

UC-EMLP (22X22) SR CUS - Plastic label

0826987

<https://www.phoenixcontact.com/us/products/0826987>



Classifications

ECLASS

ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-EMLP (22X22) SR CUS - Plastic label

0826987

<https://www.phoenixcontact.com/us/products/0826987>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com