

PML-W301 (52X26) - Warning label



0830461

<https://www.phoenixcontact.com/us/products/0830461>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Sheet, yellow/black, labeled: Lightning flash and warning in German, English, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 4, text field height: 26 mm, text field width: 52 mm



Commercial data

Item number	0830461
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG21
Product key	BG2614
Catalog page	Page 377 (C-3-2019)
GTIN	4046356717854
Weight per piece (including packing)	5.68 g
Weight per piece (excluding packing)	5.57 g
Customs tariff number	39199080
Country of origin	DE

PML-W301 (52X26) - Warning label



0830461

<https://www.phoenixcontact.com/us/products/0830461>

Technical data

Product properties

Product type	Warning label printed
Area of application	Warning labels
	Warning identification according to ISO 7010
Type	Rectangle

Marking

Number of individual labels	4
Number of individual labels per row	1
Printing	Lightning flash and warning in German, English
Identification technology	Office laser printing

Dimensions

Width	52 mm
Height	26 mm
Length	26 mm
Diameter	0.00 mm

Text field

Text field width	52 mm
Text field height	26 mm

Material specifications

Color	yellow/black
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

PML-W301 (52X26) - Warning label



0830461

<https://www.phoenixcontact.com/us/products/0830461>

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

PML-W301 (52X26) - Warning label



0830461

<https://www.phoenixcontact.com/us/products/0830461>

Classifications

ECLASS

ECLASS-11.0	40200203
ECLASS-13.0	40200203
ECLASS-12.0	40200203

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-W301 (52X26) - Warning label



0830461
<https://www.phoenixcontact.com/us/products/0830461>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com