

RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector front mounting, angled rotatable, Screw locking mechanism, M23, number of positions: 12, contact connection type: Pin, Axial O-ring, shielded: yes, flange dimensions: 26 mm x 26 mm, number of positions: 12, connection method: Crimp connection, series: RF



Your advantages

- Easy connection, thanks to infinitely adjustable cable outlet direction up to 310°
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1607233
Packing unit	16 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAGM
Catalog page	Page 112 (C-2-2019)
GTIN	4046356175012
Weight per piece (including packing)	132.8 g
Weight per piece (excluding packing)	117.019 g
Customs tariff number	85366990
Country of origin	DE

RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Mounting

Mounting type	Front mounting/square flange 4x Ø 3,2 mm
Assembly note	4x Ø 3,2 mm

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Signal
Application	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

Dimensions

Housing	
Flange dimensions	26 mm x 26 mm

Material specifications

Seal material	FPM
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact	
Contact diameter	1 mm
Max. current	8 A
Nominal voltage U_N	48 V AC 74 V DC
Overshoot category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection	
Connection method	Crimp connection

RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Contact connection type	Pin
-------------------------	-----

Connector

Type	angled rotatable
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m

RF-12P1N8AAD00 - Device connector front mounting




1607233

<https://www.phoenixcontact.com/us/products/1607233>

Drawings

Dimensional drawing



Dimensional drawing


RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Dimensional drawing



Installation dimensions


RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Schematic diagram



Contact chamber numbering (view of plug-in side), standard pin

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607233>

cUL Recognized				
Approval ID: E153698-20090723				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	5 A	20	-

UL Recognized				
Approval ID: E153698-20090723				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	5 A	20	-

RF-12P1N8AAD00 - Device connector front mounting

1607233

<https://www.phoenixcontact.com/us/products/1607233>



Classifications

ECLASS

ECCLASS-13.0	27440109
--------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com