

ICE50-R122X67-A1 - Heatsink

1118305

<https://www.phoenixcontact.com/us/products/1118305>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Heatsink for housing series: ICS, material: Aluminum, anodized, product range: ICS50-..122X..., width: 67.4 mm, height: 50.1 mm, Individual milling possible.



Your advantages

- Heatsinks enable the finished devices to be used in thermally demanding applications
- Extensive thermal simulations help achieve the optimum arrangement of components on the printed circuit board
- Customized heatsinks for reliable heat dissipation
- Simplified engineering process: all the services needed for your specific device design
- Tailored system solution comprised of a housing, connection technology, heatsink, and additional accessories

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1118305 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC09 |
| Product key | ACHAEF |
| GTIN | 4063151044985 |
| Weight per piece (including packing) | 372.6 g |
| Weight per piece (excluding packing) | 372.6 g |
| Customs tariff number | 76169990 |
| Country of origin | CN |

Technical data


Notes

| | |
|---------|---|
| General | Individual milling possible. |
| General | Please observe the application note in the download area. |
| General | The R_{th} diagram shows the application, free-hanging (vertical) in the direction of flow. |

Product properties

| | |
|----------------|---------------|
| Product type | Heatsink |
| Housing type | Heatsink |
| Housing series | ICS |
| Product family | ICS50..122X.. |

Dimensions

| Dimensional drawing | |
|--------------------------|--|
| |  |
| Width | 67.4 mm |
| Height | 50.1 mm |
| Length | 127.5 mm |
| Base panel thickness [b] | 5.8 mm |

Material specifications

| | |
|-----------------------------|---|
| Color () | aluminum color |
| Material | Aluminum |
| Surface characteristics | anodized |
| Thermal resistance R_{th} | 1.39 K/W (At ΔT 65 K for ambient temperature) |
| | 2.57 K/W (At ΔT 5 K for ambient temperature) |

Environmental and real-life conditions

| Vibration test | |
|------------------------|-----------------------------|
| Specification | IEC 60068-2-6:2007-12 |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration | 2g (58.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h |

ICE50-R122X67-A1 - Heatsink

1118305

<https://www.phoenixcontact.com/us/products/1118305>



| | |
|-----------------|-------------------|
| Test directions | X-, Y- and Z-axis |
|-----------------|-------------------|

Shocks

| | |
|--------------------------------|-----------------------------------|
| Specification | IEC 60068-2-27:2008-02 |
| Pulse shape | Semi-sinusoidal |
| Acceleration | 15g |
| Shock duration | 11 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

Test for substances that would hinder coating with paint or varnish

| | |
|---------------|--------------------|
| Specification | VDMA 24364:2018-05 |
| Result | Test passed |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |

Mounting


| | |
|---------------|------|
| Mounting type | Slot |
|---------------|------|

Packaging specifications

| | |
|-------------------|---------------|
| Type of packaging | Box packaging |
|-------------------|---------------|

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.


ICE50-R122X67-A1 - Heatsink

1118305

<https://www.phoenixcontact.com/us/products/1118305>



Diagram



ICE50-R122X67-A1 - Heatsink

1118305

<https://www.phoenixcontact.com/us/products/1118305>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27260501 |
| ECLASS-15.0 | 27260501 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001143 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32131000 |
|-------------|----------|

ICE50-R122X67-A1 - Heatsink

1118305

<https://www.phoenixcontact.com/us/products/1118305>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com