

CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert



1157964

<https://www.phoenixcontact.com/us/products/1157964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 male insert, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A (IEC 60512-27-100:2008, TIA-568-C.2:2009), material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, Ethernet

Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting
- Future-proof due to CAT6_A with 10 Gbps
- 360° shielding ensures reliable transmission, even in industrial applications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1157964 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB10 |
| Product key | ABNAAB |
| GTIN | 4063151163914 |
| Weight per piece (including packing) | 21 g |
| Weight per piece (excluding packing) | 11.772 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

1157964

<https://www.phoenixcontact.com/us/products/1157964>

Technical data

Product properties

| | |
|----------------------|-----------------------------|
| Product type | Data connector (cable side) |
| Series | HC-M-RJ45-AD-I |
| Type | RJ45 |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Connection profile | RJ45 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Cable outlet | straight |
| Positions/contacts | 8P8C |

Insulation characteristics

| | |
|---------------------|---|
| Ovvoltage category | I |
| Degree of pollution | 2 |

Electrical properties

| | |
|---|--|
| Rated voltage (III/3) | 72 V (DC) |
| Rated current | 1.75 A |
| Contact resistance | < 20 mΩ (Contact) < 100 mΩ (shield) |
| Insulation resistance | > 500 MΩ |
| Contact resistance per contact pair | < 20 Ω |
| Contact resistance | > 10 mΩ (Wire – IDC) 0.005 Ω (Litz wires – IDC) |
| Transmission speed | 10 Gbps |
| Transmission characteristics (category) | CAT6 _A |
| Transmission speed | 10 Gbps |
| Power transmission | PoE++ in accordance with: IEEE 802.3bt |
| Wave impedance | 100 Ω |

Connection data

Connection technology

| | |
|----------------------------------|---|
| Connection method | Insulation displacement connection |
| Connection cross section AWG | 26 ... 24 (solid) 26 ... 24 (flexible) |
| Conductor cross section | 0.14 mm ² ... 0.22 mm ² (solid) 0.14 mm ² ... 0.22 mm ² (flexible) |
| Connection in acc. with standard | IEC 60603-7-51 |
| Cable outlet, angle | 180 |

CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert

1157964

<https://www.phoenixcontact.com/us/products/1157964>



Dimensions

| | |
|--------|---------|
| Width | 13.6 mm |
| Height | 43.4 mm |
| Length | 10.5 mm |

Material specifications

| | |
|--|-------|
| Flammability rating according to UL 94 | V0 |
| Housing material | Metal |
| Housing surface material | Ni |
| Contact material | CuSn |
| Contact surface material | Au/Ni |
| Material for screw connection | PA |

Cable/line

| | |
|--------------------------|---------------|
| External cable diameter | 5 mm ... 9 mm |
| External cable diameter | 5 mm ... 9 mm |
| Test voltage Core/Core | 1000 V |
| Test voltage Core/Shield | 1500.00 V |
| Wave impedance | 100 Ω |

Mechanical properties

| | |
|-------------------------------------|-----------|
| Mechanical data | |
| Insertion/withdrawal cycles | ≥ 750 |
| Insertion force per signal contact | < 20.00 N |
| Extraction force per signal contact | < 20 N |

Environmental and real-life conditions

| | |
|--------------------|------------------------|
| Test specification | |
| Type of test | Vibration test |
| Specification | IEC 60068-2-6 |
| Frequency | 10-500 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm |
| Acceleration | 50.00 m/s ² |
| Test duration | 20.00 s |

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

Mounting

| | |
|---------------|--------------------|
| Mounting type | For field assembly |
|---------------|--------------------|

1157964

<https://www.phoenixcontact.com/us/products/1157964>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1157964>

| cULus Recognized | | | | |
|-------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| Approval ID: E335024-20170228 | | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 56.5 V | 1.75 A | - | - |

CUC-INI-C1ZNI-S/R4IE10G8 - RJ45 male insert

1157964

<https://www.phoenixcontact.com/us/products/1157964>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440114 |
| ECLASS-15.0 | 27440114 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002636 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com