

THERMOMARK GO.K - Thermal transfer printer



1184146

<https://www.phoenixcontact.com/us/products/1184146>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile thermal transfer printer for marking materials in cartridge format. The printer can print materials in continuous format up to a material width of 24 mm.

Product description

The THERMOMARK GO.K handheld printer is ideal for fast identification on site. The thermal transfer printer is robust, easy to use, and offers versatile functions. It processes continuous media for terminal marking, cable and wire marking, equipment marking, and plant marking.

Scope of supply:

THERMOMARK GO.K, brief instructions

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- 8 different bar codes and over 300 symbols can be integrated; up to 20 projects can be created and stored directly on the device
- Printing of self-adhesive, non-sticky labels and shrink sleeves
- The THERMOMARK GO.K prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon
- Intuitive user guidance thanks to a well-structured menu and direct input keys
- Alternative control via the PROJECT complete software

Commercial data

Item number	1184146
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4063151223441
Weight per piece (including packing)	858.09 g
Weight per piece (excluding packing)	676.46 g
Customs tariff number	84433210
Country of origin	CN

THERMOMARK GO.K - Thermal transfer printer

1184146

<https://www.phoenixcontact.com/us/products/1184146>



Technical data

Product properties

Product type	Marking system
Scope of supply	THERMOMARK GO.K, brief instructions

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Device properties

Print width	24 mm
Print resolution	203 dpi
Operating system	Windows 10, Windows Server 2016, Windows Server 2019, Windows Server 2022

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	-----------------------------------------

Dimensions

Width	98 mm
Height	69 mm
Length	230 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
---------------------------------	----------------

THERMOMARK GO.K - Thermal transfer printer

1184146

<https://www.phoenixcontact.com/us/products/1184146>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1184146>



cULus Listed

Approval ID: E140403

UAE-RoHS

Approval ID: 13802_E22-04-033963

THERMOMARK GO.K - Thermal transfer printer

1184146

<https://www.phoenixcontact.com/us/products/1184146>



Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

UNSPSC

UNSPSC 21.0	43212100
-------------	----------

THERMOMARK GO.K - Thermal transfer printer

1184146

<https://www.phoenixcontact.com/us/products/1184146>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com