

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB PCB connectors, connection direction of the connector to the PCB: 180 °, number of positions: 9, 5 GBit/s, Wave soldering

Your advantages

- Optimized for wave soldering
- Data transmission up to 5 Gbps
- Comfortable tray packing

Commercial data

Item number	1332638
Packing unit	140 pc
Minimum order quantity	140 pc
Sales key	AB14
Product key	ABNDAB
GTIN	4063151630300
Weight per piece (including packing)	2.36 g
Weight per piece (excluding packing)	2.36 g
Customs tariff number	85366930
Country of origin	CN

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Technical data

Product properties

Product type	Data connector (device side)
Orientation to PCB	180.00 °
Number of positions	9 ()
Transmission speed	5 GBit/s

Electrical properties

Rated voltage	30 V
Rated surge voltage	1.5 kV
Rated current	1.8 A
Contact resistance	30 mΩ
Frequency range	20 Hz ... 500 Hz
Insulation resistance	1000 MΩ
Transmission speed	5 Gbps
Transmission characteristics (category)	USB 3.2 Gen 1
Transmission speed	5 GBit/s
Power transmission	54 W

Connection data

Connection technology	
Connection method	Solder connection

Dimensions

Width	14.45 mm
Height	7.4 mm
Length	14.8 mm
Orientation to PCB	180.00 °

Material specifications

Color (Housing)	blue (RAL 5015)
Material Contact	Brass
Material Contact surface	Gold over nickel
Material Contact carrier	PA 4T
Material Housing	Metal

Cable/line

Halogen-free	yes
Flame resistance	UL 94 V0

Mechanical properties

Mechanical data	
-----------------	--

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Insertion/withdrawal cycles	> 5000
Insertion force	35 N
Withdrawal force	< 10 N

Environmental and real-life conditions

Test specification

Specification	EIA 364-1000
Frequency	20-500 Hz
Sweep speed	1 octave/min
Acceleration	3.10 m/s ²
Test duration	15.00 min
Contact resistance R ₁	30.00 mΩ

Test specification

Specification	60068-2-27
Acceleration	30.00 g
Number of shocks per direction	18.00

Ambient conditions

Degree of protection (when plugged in)	IP20
Degree of protection (not plugged in)	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Standards and regulations

Flame resistance	UL 94 V0
------------------	----------

Mounting

Mounting type	Wave soldering
---------------	----------------

Processing notes

Process	Wave soldering
Classification temperature T _c	260 °C

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors




1332638

<https://www.phoenixcontact.com/us/products/1332638>

Drawings

Diagram



Classification wave soldering profile

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-USB3.0-J1ST-S/UAF-THT - USB PCB connectors



1332638

<https://www.phoenixcontact.com/us/products/1332638>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com