

US-EMP (27X15) SR CUS - Snap-in markers

0830038

<https://www.phoenixcontact.com/us/products/0830038>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, can be ordered: by card, silver, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 27, text field height: 15 mm, text width: 27 mm



Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0830038
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356614009
Weight per piece (including packing)	14.57 g
Weight per piece (excluding packing)	14.57 g
Country of origin	PL

US-EMP (27X15) SR CUS - Snap-in markers

0830038

<https://www.phoenixcontact.com/us/products/0830038>



Technical data

Product properties

Product type	Gerätemarker
Marking	
Number of individual labels	27
Number of individual labels per row	3
Identification technology	Thermotransfer

Dimensions

Width	26.90 mm
Height	14.90 mm
Depth	0.50 mm
Length	14.9 mm

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	silver
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
UV resistance	
Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 25 °C / 35 ... 65 % relative humidity. Storage in a cool and dry place is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	35 % ... 65 %
Shelf life	12 months (see packaging date)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMP (27X15) SR CUS - Snap-in markers

0830038

<https://www.phoenixcontact.com/us/products/0830038>



Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

US-EMP (27X15) SR CUS - Snap-in markers

0830038

<https://www.phoenixcontact.com/us/products/0830038>



Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (27X15) SR CUS - Snap-in markers

0830038

<https://www.phoenixcontact.com/us/products/0830038>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com