

LS-EMLP (17X7) SR - Device marker



0831707

<https://www.phoenixcontact.com/us/products/0831707>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, silver, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 220, text field height: 7 mm, text field width: 17 mm



Your advantages

- Stick-on device marking
- Prefabricated device markers in the proven laser-sheet format for ideal positioning in the marking device
- High contrast due to the silver top layer with black marking

Commercial data

Item number	0831707
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG19
Product key	BG241D
GTIN	4046356926485
Weight per piece (including packing)	36.12 g
Weight per piece (excluding packing)	36.12 g
Customs tariff number	39203000
Country of origin	DE

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	220
Identification technology	Direct laser marking

Dimensions

Width	17.00 mm
Height	7.00 mm
Depth	0.85 mm

Material specifications

Foil strength	800 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	silver-colored
Material	ABS
Base element material	ABS
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilem test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
---------------	---------------------------------

LS-EMLP (17X7) SR - Device marker



0831707

<https://www.phoenixcontact.com/us/products/0831707>

Test duration	240 h
---------------	-------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

LS-EMLP (17X7) SR - Device marker



0831707

<https://www.phoenixcontact.com/us/products/0831707>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLP (17X7) SR - Device marker



0831707

<https://www.phoenixcontact.com/us/products/0831707>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com