

VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power distributor, degree of protection: IP65, number of positions: 5, material: Metal, connection method: Coupling, cable outlet: straight, color: black, Universal



Product description

Power H distributor

Commercial data

Item number	1405387
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	AB17
Product key	ABNOIA
GTIN	4046356419918
Weight per piece (including packing)	132.1 g
Weight per piece (excluding packing)	132.1 g
Customs tariff number	85366990
Country of origin	DE

VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Network distributor box
Type	Version 14
Sensor type	Universal
Number of positions	5
Connection profile	Power
Number of slots	4
Cable outlet	straight

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated voltage (II/2)	630 V
Rated voltage (III/2)	400 V
Rated voltage (III/3)	24 V
	250 V
Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV
Rated current	16 A (at 20 °C)
	16 A
Nominal voltage U_N	24 V
Nominal current I_N	16 A
Transmission medium	Copper

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Dimensions

Width	73 mm
Height	35 mm
Length	58 mm

VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Material specifications

Color	black
Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	Metal
Contact surface material	Gold over nickel
Contact carrier material	PA

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

Mounting

Mounting type	Screw mounting
Assembly note	When mounting the device on a level surface, use the VS-PPC-J-M mounting foot

VS-PPC-J-4X-1227 - Power distributor


1405387

<https://www.phoenixcontact.com/us/products/1405387>



Drawings

Circuit diagram



VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405387>

 cUL Recognized Approval ID: E118976-20080903				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	24 V	14 A	-	-

 UL Recognized Approval ID: E118976-20080903				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	24 V	16 A	-	-

VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440390

ETIM

ETIM 9.0	EC004746
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-J-4X-1227 - Power distributor



1405387

<https://www.phoenixcontact.com/us/products/1405387>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com