

# HC-M-01-COAX-CK1,6-75-M - Connector



1066962

<https://www.phoenixcontact.com/us/products/1066962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, number of positions: 1, power contacts: 0, control contacts: 1, Pin, Crimp connection, 48 V, 10 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, external cable diameter: 3 mm ... 9.5 mm, application: COAX, 75 Ω

## Commercial data

Item number	1066962
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACB
GTIN	4055626733975
Weight per piece (including packing)	32.8 g
Weight per piece (excluding packing)	31.83 g
Customs tariff number	85389099
Country of origin	CN

# HC-M-01-COAX-CK1,6-75-M - Connector



1066962

<https://www.phoenixcontact.com/us/products/1066962>

## Technical data

### Notes

General	Order crimp contacts separately
General	The potential of the EMC connector housing is isolated from the potential of the heavy connector.
General	Clamps for the clamping range of 3 mm - 6 mm and 6 mm - 9.5 mm
General	Can be used in Item No.: 1417374 HC-M-02-EMC-M
General	For 75 Ω coaxial cables

### Product properties

Product type	EMC insert, modular
Series	HC-M-EMV
Application	COAX
Number of positions	1
Connection profile	1
No. of cable outlets	1
No. of power contacts	0
No. of control contacts	1
Contact material type	turned rolled
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	0.8 kV
Rated current	10 A
Wave impedance	75 Ω

### Connection data

#### Connection technology

Connection technology	Crimp connection
-----------------------	------------------

#### Conductor connection


Conductor cross section	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm

### Dimensions

# HC-M-01-COAX-CK1,6-75-M - Connector

1066962

<https://www.phoenixcontact.com/us/products/1066962>

Dimensional drawing	
Height	15.5 mm
Length	46.2 mm

## Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

## Material specifications

Material Line conductor	Zinc alloy
Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Au
Contact carrier material	PC

## Cable/line

External cable diameter	3 mm ... 9.5 mm
Stripping length of the individual wire	8 mm
Wave impedance	75 $\Omega$

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	$\geq 500$
-----------------------------	------------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

## Mounting

Assembly note	Sheath stripping length: 23 mm, shield length: 13 mm, inner conductor stripping length: 8 mm
---------------	--

# HC-M-01-COAX-CK1,6-75-M - Connector




1066962

<https://www.phoenixcontact.com/us/products/1066962>


## Drawings

Dimensional drawing



Male insert

Diagram



Attenuation curve

# HC-M-01-COAX-CK1,6-75-M - Connector



1066962

<https://www.phoenixcontact.com/us/products/1066962>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1066962>

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	50 V	10 A	-	-

# HC-M-01-COAX-CK1,6-75-M - Connector



1066962

<https://www.phoenixcontact.com/us/products/1066962>

## Classifications

### ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# HC-M-01-COAX-CK1,6-75-M - Connector



1066962

<https://www.phoenixcontact.com/us/products/1066962>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)