

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Narrow Ethernet switch, four RJ45 ports, one SFP port, with 10/100/1000 Mbps on all ports, automatic data transmission speed detection, autocrossing function, and QoS

## Your advantages

- Jumbo frame support (frame size up to 9216 bytes/frame)
- RJ45 ports support a transmission speed of 10/100/1000 Mbps
- QoS-prioritized (Quality of Service) messages
- Local diagnostic indicators with LEDs
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Enhanced traffic prioritization for automation protocols
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET conformance Class A for real-time data exchange, alarms, and diagnostics
- Auto negotiation and autocrossing detection simplifies installation and setup

## Commercial data

Item number	1085173
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN20
Product key	DNN116
GTIN	4055626834665
Weight per piece (including packing)	219.4 g
Weight per piece (excluding packing)	136 g
Customs tariff number	85176200
Country of origin	TW

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



## Technical data

### Dimensions

Width	22.5 mm
Height	117 mm
Depth	84 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Material specifications

Housing material	Polycarbonate fiber reinforced
------------------	--------------------------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

#### Ethernet (RJ45)

Number of interfaces	4
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	4 (RJ45 ports)
Input buffer	1.5 Mbits
Output buffer	1.5 Mbits

#### Ethernet (SFP)

Number of interfaces	1
Connection method	SFP
Transmission speed	100/1000 Mbps (full duplex)
Transmission physics	Depending on the SFP module
Transmission length	up to 40 km (Depending on the fiber/SFP module used)
Signal LEDs	Data receive, link status
No. of channels	1 (SFP port)

### Product properties

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



Product type	Switch
Product family	Unmanaged Switch 1000
MTTF	77.4 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) 949.7 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) 828.9 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
Basic functions	Unmanaged switch Autonegotiation Store and Forward switching mode

## Switch functions

Basic functions	Unmanaged switch Autonegotiation Store and Forward switching mode
PROFINET conformance class	Conformance Class A
MAC address table	4k
Status and diagnostic indicators	LEDs: $U_S$ , link and activity per port
Additional functions	100 BASE-TX/100BASE-FX (IEEE 802.3u) Jumbo frames (Max. 9,216 bytes) Quality of Service (QoS) prioritization (IEEE 802.1p) Energy-efficient Ethernet (IEEE 802.3az) Gigabit Ethernet 1000BASE-T (IEEE 802.3ab) 10Base-T (IEEE 802.3)

## Security functions

Basic functions	Unmanaged switch Autonegotiation Store and Forward switching mode
-----------------	---

## Electrical properties

Maximum power dissipation for nominal condition	3.762 W (at 24 V DC)
Transmission medium	Copper

## Supply

Supply voltage (DC)	24 V DC
Supply voltage (AC)	24 V AC (50/60 Hz)
Supply voltage range	9 V DC ... 32 V DC 18 V AC ... 30 V AC (50/60 Hz)
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Max. current consumption	418 mA (at 9 V DC)
Typical current consumption	48 mA (at 24 V DC)

## Connection data

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch



1085173

<https://www.phoenixcontact.com/us/products/1085173>

## Connection technology

Connection name	Power supply
pluggable	yes

## Power supply

Connection method	Push-in spring connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Stripping length	10 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (maximum)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	30g (EN 60068-2-27)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)
Air pressure (storage/transport)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)

## Approvals

### Conformity/Approvals

UL, USA / Canada	UL 61010-1, UL 61010-2-201, UL 62368-1 Class I, Div. 2, Groups A, B, C, D, T4 Class I, Zone 2, Group IIC, T4
FCC	Title 47 Part 15 Subpart B:2018 Class A

## EMC data

Noise immunity	EN 61000-6-2:2019
Noise emission	
Standards/regulations	EN_61000-6-4:2019

## System properties

Functionality	Unmanaged switch
---------------	------------------

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



Basic functions

Autonegotiation

Store and Forward switching mode

## Signaling

Status display

LEDs:  $U_S$ , link and activity per port

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085173>



**KC**

Approval ID: R-R-PCK-1085173



**cULus Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E140403



**cUL Listed**

Approval ID: E196811



**UL Listed**

Approval ID: E196811

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



## Classifications

### ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

### ETIM

ETIM 9.0	EC000734
----------	----------

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# FL SWITCH 1104N-SFP - Industrial Ethernet Switch

1085173

<https://www.phoenixcontact.com/us/products/1085173>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4180edc0-62a9-4704-8396-6a75f05f5d53

### EF3.0 Climate Change

CO2e kg	4.606 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)