

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 8, 1 Gbps, CAT5, cable outlet: straight, Ethernet, 4 x 2 x AWG 24/7, UTP, gray



Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1410596 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB11 |
| Product key | ABNABM |
| GTIN | 4046356900256 |
| Weight per piece (including packing) | 54.2 g |
| Weight per piece (excluding packing) | 51.2 g |
| Customs tariff number | 85444210 |
| Country of origin | CN |

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable

1410596

<https://www.phoenixcontact.com/us/products/1410596>



Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Product family | RJ45 BASIC IE8 CAT5 |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Number of slots | 1 |
| Shielded | no |
| Cable outlet | straight |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Electrical properties

| | |
|---|-----------------------|
| Rated voltage (III/3) | 72 V (DC) |
| Nominal voltage U_N | 48 V |
| Nominal current I_N | 1 A |
| Transmission medium | Copper |
| Transmission speed | up to 1 Gbps |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |
| Transmission speed | 1 Gbps |

Mechanical properties

| | |
|-------------------------------------|---------|
| Mechanical data | |
| Insertion force per signal contact | 50.00 N |
| Extraction force per signal contact | 30 N |

Material specifications

| | |
|--|-----|
| Flammability rating according to UL 94 | V0 |
| Outer sheath, material | PVC |

Connector

| | |
|-----------------------------|----------------------|
| Connection 1 | |
| Type | Plug straight RJ45 |
| Shielded | yes |
| Handle color | gray |
| Material | CuSn (Contact) |
| | Au (Contact surface) |
| | PVC (Housing) |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 80 °C |
|---------------------------------|------------------|

Connection 2

| | |
|---------------------------------|---|
| Type | Plug straight RJ45 |
| Shielded | yes |
| Handle color | gray |
| Material | CuSn (Contact) Au (Contact surface) PVC (Housing) |
| Insertion/withdrawal cycles | ≥ 750 |
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 80 °C |

Cable/line

| | |
|--------------|--------|
| Cable length | 2.00 m |
|--------------|--------|

| | |
|-----------------------------------|-----------------------------------|
| Ethernet, CAT5, 4-pair, UTP [UTP] | |
| Number of positions | 8 |
| Shielded | no |
| Cable type | Ethernet, CAT5, 4-pair, UTP [UTP] |
| Conductor structure | 4 x 2 x AWG 24/7, UTP |
| AWG signal line | 24 |
| Outer sheath, material | PVC |
| External sheath, color | gray |

Environmental and real-life conditions

| | |
|---------------------------------|-----------------------------------|
| Ambient conditions | |
| Degree of protection | IP20 (RJ45 connector) |
| | IP20 |
| Ambient temperature (operation) | -25 °C ... 80 °C (RJ45 connector) |

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable




1410596

<https://www.phoenixcontact.com/us/products/1410596>

Drawings

Schematic diagram



Connector pin assignment plug RJ45


NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

Circuit diagram



Contact assignment of RJ45 plugs

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1410596>



EAC

Approval ID: 19060508

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

NBC-R4AC/2,0-UTP GY/R4AC - Patch cable



1410596

<https://www.phoenixcontact.com/us/products/1410596>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com