

NBC-FSBPXS/1,0-94F/R4AC-10G - Network cable

1412315

<https://www.phoenixcontact.com/us/products/1412315>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, degree of protection: IP67/IP20, cable length: 1 m, number of positions: 8, 10 Gbps, CAT6_A, cable outlet: straight, Ethernet, 4x2xAWG26/7; S/FTP, water blue RAL 5021

Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

Commercial data

Item number	1412315
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNPAC
GTIN	4046356953566
Weight per piece (including packing)	85.3 g
Weight per piece (excluding packing)	77.983 g
Customs tariff number	85444290
Country of origin	PL

Technical data

Product properties

Product type	Circular connectors (device side)
Type	M12
Sensor type	Ethernet
Number of positions	8
Number of slots	1
Shielded	yes
Coding	X
Cable outlet	straight

Insulation characteristics

Degree of pollution	3
---------------------	---

Material specifications

Material	Zinc die-cast (nickel-plated)
Flammability rating according to UL 94	V2
Seal material	FKM
Material of grip body	Zinc die-cast, nickel-plated
Contact material	CuZn
Contact surface material	gold-plated
Contact carrier material	PPA
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PUR

Electrical properties

Rated voltage (III/3)	72 V (DC)
Nominal voltage U_N	48 V
Nominal current I_N	0.5 A
Transmission medium	Copper
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 _A
Transmission speed	10 Gbps

Connector

Connection 1

Type	Flush-type female connector straight M12
Locking type	SPEEDCON
Coding type	X (Data)
Insertion/withdrawal cycles	>= 100
Degree of protection	IP65/IP67

Connection 2

NBC-FSBPXS/1,0-94F/R4AC-10G - Network cable

1412315

<https://www.phoenixcontact.com/us/products/1412315>



Type	Plug straight RJ45
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Cable/line

Cable length	1.00 m
--------------	--------

Ethernet 10 Gbit [94F]

Dimensional drawing



Cable weight	42 kg/km
UL AWM Style	20963 (80°C/30 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet 10 Gbit [94F]
Conductor structure	4x2xAWG26/7; S/FTP
Signal runtime	5.13 ns/m
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	1.04 mm
External cable diameter	6.40 mm ± 0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, outer sheath	0.65 mm
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined foil
Overall twist	4 pairs for core
Optical shield covering	70 %
Insulation resistance	$\geq 500 \text{ M}\Omega \text{ km}$
Loop resistance	$\leq 290.00 \text{ }\Omega \text{ /km}$
Wave impedance	100 $\Omega \pm 5$ Ω (at 100 MHz)
Cable capacity	47 nF/km
Nominal voltage, cable	$\leq 100 \text{ V}$

NBC-FSBPXS/1,0-94F/R4AC-10G - Network cable

1412315

<https://www.phoenixcontact.com/us/products/1412315>



Test voltage Core/Core	700 V (50 Hz, 1 min.)
Test voltage Core/Shield	700.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	52 mm
Tensile strength	≤ 100 N
Near end crosstalk attenuation (NEXT)	75.3 dB (with 1 MHz) 66.3 dB (at 4 MHz) 61.8 dB (at 8 MHz) 60.3 dB (at 10 MHz) 57.2 dB (at 16 MHz) 55.8 dB (at 20 MHz) 54.3 dB (at 25 MHz) 52.8 dB (at 31.25 MHz) 48.4 dB (at 62.5 MHz) 45.3 dB (at 100 MHz) 40.8 dB (at 200 MHz) 39.3 dB (at 250 MHz) 38.1 dB (at 300 MHz) 38.1 dB (at 400 MHz) 38.1 dB (at 500 MHz)
Power-summed near end crosstalk attenuation (PSNEXT)	72.3 dB (with 1 MHz) 63.3 dB (at 4 MHz) 58.8 dB (at 8 MHz) 57.3 dB (at 10 MHz) 54.2 dB (at 16 MHz) 52.8 dB (at 20 MHz) 51.3 dB (at 25 MHz) 49.9 dB (at 31.25 MHz) 45.4 dB (at 62.5 MHz) 42.3 dB (at 100 MHz) 37.8 dB (at 200 MHz) 36.3 dB (at 250 MHz) 35.1 dB (at 300 MHz) 33.3 dB (at 400 MHz) 31.8 dB (at 500 MHz)
Return attenuation (RL)	20 dB (with 1 MHz) 23 dB (at 4 MHz) 24.5 dB (at 8 MHz) 25 dB (at 10 MHz) 25 dB (at 16 MHz) 25 dB (at 20 MHz) 24.2 dB (at 25 MHz)

NBC-FSBPXS/1,0-94F/R4AC-10G - Network cable

1412315

<https://www.phoenixcontact.com/us/products/1412315>



	23.3 dB (at 31.25 MHz)
	20.7 dB (at 62.5 MHz)
	19 dB (at 100 MHz)
	16.4 dB (at 200 MHz)
	15.6 dB (at 250 MHz)
	15.6 dB (at 300 MHz)
	15.6 dB (at 400 MHz)
	15.6 dB (at 500 MHz)
Shield attenuation	3.1 dB (with 1 MHz)
	5.7 dB (at 4 MHz)
	8 dB (at 8 MHz)
	8.9 dB (at 10 MHz)
	11.2 dB (at 16 MHz)
	12.6 dB (at 20 MHz)
	14.1 dB (at 25 MHz)
	15.8 dB (at 31.25 MHz)
	22.5 dB (at 62.5 MHz)
	28.7 dB (at 100 MHz)
	41.4 dB (at 200 MHz)
	46.6 dB (at 250 MHz)
	51.4 dB (at 300 MHz)
	60.1 dB (at 400 MHz)
	67.9 dB (at 500 MHz)
	≥ 80.00 dB (at 30 ... 100 MHz)
Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2
	in accordance with UN ECE-R 118.03
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (installation)	-20 °C ... 80 °C


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (M12 socket)
	IP20 (RJ45 connector)
	IP67/IP20
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 60 °C (Plug / socket)


Drawings

Schematic diagram



M12 socket pin assignment, 8-pos, view of socket side

Schematic diagram



Connector pin assignment plug RJ45

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412315>



EAC

Approval ID: 19060508

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 9.0	EC003570
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	dba989a0-4c52-416d-8289-194942132077

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com