

# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, Ethernet CAT6<sub>A</sub> (10 Gbps), 8-pos., halogen-free, shielded, insulation displacement connection, housing material: zinc die-cast, nickel-plated, outer cable diameter of 5 mm ... 9.7 mm

## Your advantages

- Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- Safe use in the field, thanks to a high degree of protection
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

## Commercial data

Item number	1414412
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF31
Product key	AF6EFI
GTIN	4055626025490
Weight per piece (including packing)	62.8 g
Weight per piece (excluding packing)	62 g
Customs tariff number	85366990
Country of origin	DE

# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---

### Mounting

Assembly note	If the conductor is to be reconnected, it must be cut off above the last contact point.
---------------	---

### Product properties

Product type	Cable connector
Sensor type	Ethernet
Number of positions	8
No. of cable outlets	2
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Length	83 mm
Wrench size, union nut	15 mm
Wrench size, counter nut	17 mm

### External dimensions

Outside diameter	5 mm ... 9.7 mm
------------------	-----------------

### Connection data

Connection technology	
Connection method	Insulation displacement connection
Frequency of connections between conductors of the same cross section	10

Conductor connection	
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	Class 2-6
Tightening torque	5 Nm (Pressure nut)

# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



Wrench size, union nut	15 mm
Wrench size, contact carrier	17 mm
Wire diameter including insulation	0.75 mm ... 2 mm
Tightening torque	5 Nm (Pressure nut)

## Connection assignment

Contact   Color (signal designation)   Contact (optional)	1 = WHOG (D1+) 2 = OG (D1-) 3 = WHGN (D2+) 4 = GN (D2-) 5 = WHBN (D4+) 6 = BN (D4-) 7 = WHBU (D3-) 8 = BU (D3+)
---	--

## Electrical properties

Rated surge voltage	0.8 kV
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC 60 V DC
Nominal current $I_N$	0.5 A (30 W)
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 <sub>A</sub>

## Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	Zinc die-cast, nickel-plated
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated
Standards/regulations	PA 6.6
Wire insulation material	PVC / PE / PP / rubber

## Connector

Connection 1	
Head design	Cable connectors

## Cable/line

Signal type/category	Ethernet CAT6 <sub>A</sub> (IEC 11801), 10 Gbps
----------------------	---

## Environmental and real-life conditions

Ambient conditions	
--------------------	--

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C

## Standards and regulations

### Testing

Standards/regulations	PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
Standards/specifications	according to IEC 61076-2-109
Standard designation	Shock, vibration
Standards/specifications	EN 50155:2001

# SACC-CC-8QO SH ETH - Conductor connector


1414412

<https://www.phoenixcontact.com/us/products/1414412>




## Drawings

Dimensional drawing



Functional drawing



# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414412>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CC-8QO SH ETH - Conductor connector

1414412

<https://www.phoenixcontact.com/us/products/1414412>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	3.512 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)