

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, yellow/black, unmarked, can be labeled with: THERMOMARK GO, cable diameter range: 6 ... 115 mm, mounting type: Assembly with cable ties, Number of individual labels: 20, text field height: 22 mm, text field width: 55 mm

Product description

Prepunched, halogen-free MM-WMTB HF conductor markers made of polyurethane are attached to the conductor with a cable tie.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The cable markers are mounted very easily using a cable tie. Alternatively, a large number of conductors can also be bundled together in this way
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing

Commercial data

Item number	1116210
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG221E
GTIN	4063151042226
Weight per piece (including packing)	78.8 g
Weight per piece (excluding packing)	78.6 g
Customs tariff number	96121010
Country of origin	CN

MM-WMTB HF (55X25)R C1 YE/BK - Cable marker

1116210

<https://www.phoenixcontact.com/us/products/1116210>



Technical data

Product properties

Product type	Conductor marker
Marking	
Number of individual labels	20
Number of individual labels per row	1
Identification technology	Thermal transfer

Dimensions

Width	75 mm
Height	24.3 mm
Depth	0.45 mm

Material specifications

Foil strength	450 µm
Color	multicolored (RAL -) yellow (RAL 1018) black (RAL 9005)
Material	PUR
Flammability rating according to UL 94	HB
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	6 mm ... 115 mm
-------------------------	-----------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

MM-WMTB HF (55X25)R C1 YE/BK - Cable marker

1116210

<https://www.phoenixcontact.com/us/products/1116210>



Procedure	Artificial irradiation.
Temperature resistance	
Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed
Wipe resistance of inscriptions	
Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
Testing in a condensation changing climate in the presence of sulfur dioxide	
Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2
Salt spray test	
Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h
Ambient conditions	
Ambient temperature (operation)	-25 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	24 months

MM-WMTB HF (55X25)R C1 YE/BK - Cable marker

1116210

<https://www.phoenixcontact.com/us/products/1116210>



Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type

Assembly with cable ties

MM-WMTB HF (55X25)R C1 YE/BK - Cable marker

1116210

<https://www.phoenixcontact.com/us/products/1116210>



Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-WMTB HF (55X25)R C1 YE/BK - Cable marker

1116210

<https://www.phoenixcontact.com/us/products/1116210>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com