

SACC-DSIV-M12-NUT-9 THR PPI - Housing screw connection



1249211

<https://www.phoenixcontact.com/us/products/1249211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Socket, M12-Push-pull internal locking, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Flexible PCB assembly: two-piece connectors for wave and THR soldering

Commercial data

Item number	1249211
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQAAI
GTIN	4063151354213
Weight per piece (including packing)	10.57 g
Weight per piece (excluding packing)	10.273 g
Customs tariff number	74198090
Country of origin	DE

SACC-DSIV-M12-NUT-9 THR PPI - Housing screw connection



1249211

<https://www.phoenixcontact.com/us/products/1249211>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

Product properties

Product type	Circular connector housing
Thread type	M12

Connection data

Connection method	THR solder connection
Tightening torque	2 ... 3 Nm

Material specifications

Seal material	FKM
Material for screw connection	Brass, nickel-plated

Connector

Connection 1	
Head design	Socket
Head thread type	M12
Head locking type	Push-pull internal locking

Cable/line

Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation)
	-25 °C ... 85 °C (Cable, flexible installation)

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
	IP65, when in locked state

SACC-DSIV-M12-NUT-9 THR PPI - Housing screw connection



1249211

<https://www.phoenixcontact.com/us/products/1249211>

Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)
Ambient temperature (operation) (Cable, flexible installation)	-25 °C ... 85 °C (Cable, flexible installation)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 85 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010

Mounting

Mounting type	Front mounting (M14 x 1)
---------------	--------------------------

SACC-DSIV-M12-NUT-9 THR PPI - Housing screw connection



1249211

<https://www.phoenixcontact.com/us/products/1249211>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-M12-NUT-9 THR PPI - Housing screw connection



1249211

<https://www.phoenixcontact.com/us/products/1249211>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com