

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



5-pos. cable, black PVC, shielded, shielded plug, straight M12, A-coded, on free cable end with VA knurl, length: 5 m

Commercial data

Item number	1402941
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDD
GTIN	4046356637565
Weight per piece (including packing)	479.6 g
Weight per piece (excluding packing)	455.5 g
Country of origin	PL

SAC-5P-M12MS/ 5,0-927 VA - Sensor/actuator cable



1402941

<https://www.phoenixcontact.com/us/products/1402941>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	5

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Cable/line

CANopen®/DeviceNet™, PVC, black [927]

Cable weight	83 kg/km
UL AWM Style	2464 (80°C/300 V)
Number of positions	4
Shielded	yes
Cable type	CANopen®/DeviceNet™, PVC, black [927]
Signal runtime	4.46 ns/m
Conductor structure signal line	44x 0.10 mm
AWG signal line	22
Conductor structure, voltage supply	44x 0.10 mm
AWG power supply	22
Conductor cross section	2x 0.34 mm² (Signal line)
	2x 0.34 mm² (Power supply)
	1x 0.38 mm² (Drain wire)
Wire diameter incl. insulation	2.55 mm (Signal line)
	1.37 mm (Power supply)
External cable diameter	8.30 mm ±0.3 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PP (Signal line)
	PVC (Power supply)
Single wire, color	red-black, blue-white
Thickness, insulation	≥ 0.30 mm (Wire insulation power supply)
Thickness, outer sheath	≥ 1.00 mm
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	2 pairs with filler elements, around a drain wire in the center to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 56 Ω/km
Insulation resistance	≥ 20 MΩ*km

SAC-5P-M12MS/ 5,0-927 VA - Sensor/actuator cable



1402941

<https://www.phoenixcontact.com/us/products/1402941>

Wave impedance	120 Ω $\pm$ 12 Ω (f = 1 MHz)
Working capacitance	approx. 39.8 nF (Signal line, line-line)
	$\leq$ 4000 pF (Signal line, line-shield)
Nominal voltage, cable	$\leq$ 300 V
Test voltage	2000 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	67 mm
Flame resistance	in acc. with UL 1581, section 1061
Ambient temperature (operation)	-30 °C ... 80 °C

SAC-5P-M12MS/ 5,0-927 VA - Sensor/actuator cable



1402941

<https://www.phoenixcontact.com/us/products/1402941>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/ 5,0-927 VA - Sensor/actuator cable



1402941

<https://www.phoenixcontact.com/us/products/1402941>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com