

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet CAT5 (IEC 11801:2002), 8-position, Socket, straight, M12, Y-coding, THR solder connection, this item is expected to be lead-free from Q1 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1405225       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Sales key                            | AB23          |
| Product key                          | ABQAGS        |
| GTIN                                 | 4046356740180 |
| Weight per piece (including packing) | 4.7 g         |
| Weight per piece (excluding packing) | 3.141 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|--|

### Product properties

|                     |                |
|---------------------|----------------|
| Product type        | Contact insert |
| Application         | Data, signals  |
| Sensor type         | Ethernet       |
| Number of positions | 8              |
| Seal present        | no             |
| Shielded            | yes            |
| Coding              | Y              |
| Thread type         | M12            |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |  |
|---|--|
| Rated surge voltage                     | 0.8 kV   |
| Contact resistance                      | $\leq 3 \text{ m}\Omega$                             |
| Insulation resistance                   | $> 100 \text{ M}\Omega$                              |
| Nominal voltage $U_N$                   | 48 V AC (Power and data)<br>50 V DC (Power and data) |
| Nominal current $I_N$                   | 0.5 A (Data)<br>6 A (Power)                          |
| Transmission medium                     | Copper   |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002)                                |

### Connection data

|                   |                       |
|-------------------|-----------------------|
| Connection method | THR solder connection |
|-------------------|-----------------------|

### Interfaces

|                      |                                |
|----------------------|--------------------------------|
| Signal type/category | Ethernet CAT5 (IEC 11801:2002) |
|----------------------|--------------------------------|

### Dimensions

|                          |        |
|--------------------------|--------|
| Length of the solder pin | 2.3 mm |
|                          | 2.3 mm |

### Material specifications

# SACC-CI-M12FSY-8CON-L180 THR - Contact carrier

1405225

<https://www.phoenixcontact.com/us/products/1405225>



|  |      |
|--|------|
| Material Contact carrier               | PPA  |
| Material Contact                       | CuZn |
| Material Contact surface               | Au   |
| Flammability rating according to UL 94 | V0   |

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Socket   |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | Y        |

## Cable/line

|                      |                                |
|----------------------|--------------------------------|
| Signal type/category | Ethernet CAT5 (IEC 11801:2002) |
|----------------------|--------------------------------|

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection  | IP67 (correctly plugged in and locked) |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 90 °C (Plug / socket)       |
| UL Type Rating  | Type 4 (indoor use only)               |

## Packaging specifications

|                   |         |
|-------------------|---------|
| Type of packaging | Blister |
|-------------------|---------|

SACC-CI-M12FSY-8CON-L180 THR - Contact carrier


1405225

<https://www.phoenixcontact.com/us/products/1405225>

**PHÖNIX CONTACT**

## Drawings

## Schematic diagram



#### Pin assignment M12 connector, 8-pos., view socket side

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405225>

|  <b>cUL Recognized</b><br>Approval ID: E335024-20120308 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
| Power  | 56 V                  | 0.175 A               | -                 | -                    |
| Data   | 30 V                  | 0.5 A                 | -                 | -                    |

|  <b>UL Recognized</b><br>Approval ID: E335024-20120308 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine   |                       |                       |                   |                      |
| Power   | 56 V                  | 0.175 A               | -                 | -                    |
| Data  | 30 V                  | 0.5 A                 | -                 | -                    |

|  <b>cULus Recognized</b><br>Approval ID: E221474-20220114 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
| Power  | 48 V                  | 6 A                   | 18                | -                    |
| Data   | 50 V                  | 0.5 A                 | 26                | -                    |

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440223 |
| ECLASS-15.0 | 27440223 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003557 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | ae142883-89a1-493d-86bf-6d7181d905a5 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)