

PV-1P-1000,0/S04-10,0 - Cable reel

1459595

<https://www.phoenixcontact.com/us/products/1459595>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable ring, PE-X, black, 1-pos., cable length: 1000 m



Commercial data

Item number	1459595
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABLBDX
GTIN	4046356618908
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

PV-1P-1000,0/S04-10,0 - Cable reel

1459595

<https://www.phoenixcontact.com/us/products/1459595>



Technical data

Product properties

Number of positions	1
Shielded	no

Electrical properties

Max. conductor resistance	1.95 Ω/km
---------------------------	-----------

Material specifications

Outer sheath, material	PE-X
Conductor material	Tin-plated Cu litz wires

Cable/line

Cable length	10 m
--------------	------

PV1-F cables [S04]

Cable weight	127 kg/km
Number of positions	1
Shielded	no
Cable type	PV1-F cables [S04]
Conductor structure, voltage supply	80x 0.40 mm
AWG power supply	8
External cable diameter	6.90 mm ±0.2 mm
Outer sheath, material	PE-X
External sheath, color	black-gray RAL 7021
Thickness, insulation	≥ 0.50 mm (Inner sheath) ≥ 0.50 mm
Max. conductor resistance	1.95 Ω/m (at 20 °C)
Smallest bending radius, fixed installation	34.5 mm
Smallest bending radius, movable installation	69 mm
Ambient temperature (operation)	-40 °C ... 90 °C 120 °C (maximum permissible temperature at the conductor) 200 °C (permissible short-circuit temperature - maximum of 5 s)

Standards and regulations

Flame resistance	IEC 60332-1-2
Other resistance	Resistance to acids and alkalis Resistant to salt water Resistant to ozone

PV-1P-1000,0/S04-10,0 - Cable reel

1459595

<https://www.phoenixcontact.com/us/products/1459595>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com