

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, RJ45/IP20 straight on RJ45/IP20 straight, cable length: 7.5 m, number of positions: 8, CAT6<sub>A</sub>, connection cross section: AWG 26- 26, Ethernet, 2x2xAWG26/7, S/UTP, green

## Your advantages

- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Future-proof high-speed data transmission with up to 10 Gbps (CAT6<sub>A</sub>)

## Commercial data

Item number	1523704
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB11
Product key	ABNABH
GTIN	4063151989668
Weight per piece (including packing)	414.3 g
Weight per piece (excluding packing)	414.3 g
Customs tariff number	85444210
Country of origin	CN

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 STANDARD CAT6A
Sensor type	Ethernet
Number of positions	8
Shielded	yes

### Electrical properties

Rated voltage (III/2)	72 V
Power transmission	PoE++

### Connector

#### Connection 1

Dimensional drawing	
Connector pin assignment plug RJ45	

Type	RJ45 Plug, straight, 8-position
Number of positions	8
Shielded	yes
Signal type/category	Ethernet CAT6 <sub>A</sub> (IEC 11801:2002), 10 Gbps
Insertion/withdrawal cycles	≥ 750
Insertion force	30 N (per signal contact)
Withdrawal force	50 N (per signal contact)
Overshoot category	I
Degree of pollution	2
Material Contact	Brass
Material Contact surface	Au
Material Contact carrier	PC
Color (Housing)	green
Flammability rating according to UL 94	V0
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

#### Connection 2


# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

## Dimensional drawing



Connector pin assignment plug RJ45

Type	RJ45 Plug, straight, 8-position
Number of positions	8
Shielded	yes
Signal type/category	Ethernet CAT6 <sub>A</sub> (IEC 11801:2002), 10 Gbps
Insertion/withdrawal cycles	≥ 750
Insertion force	30 N (per signal contact)
Withdrawal force	50 N (per signal contact)
Overshoot category	I
Degree of pollution	2
Material Contact	Brass
Material Contact surface	Au
Material Contact carrier	PC
Color (Housing)	green
Flammability rating according to UL 94	V0
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

## Cable/line

Cable length	7.50 m
Ethernet, Type B, 8-pos., CAT5, LSZH [BC5]	
Number of positions	8
Shielded	yes
Cable type	Ethernet, Type B, 8-pos., CAT5, LSZH [BC5]
Conductor structure	2x2xAWG26/7, S/UTP
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Wire diameter incl. insulation	0.85 mm
External cable diameter	5.70 mm ±0.3 mm
Outer sheath, material	LSZH
External sheath, color	green
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wires, quantity	8
Single wire, cross section [AWG]	26

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

Thickness, outer sheath	approx. 0.70 mm
Optical shield covering	70 %
Insulation resistance	$\geq 5000 \text{ M}\Omega\text{-km}$
Loop resistance	$\leq 148.00 \text{ }\Omega/\text{km}$
Wave impedance	100 $\Omega$
Minimum bending radius, fixed installation	8 x D
Smallest bending radius, fixed installation	46 mm
Near end crosstalk attenuation (NEXT)	65.3 dB (with 1 MHz) 56.3 dB (at 4 MHz) 50.3 dB (at 10 MHz) 47.2 dB (at 16 MHz) 45.8 dB (at 20 MHz) 42.9 dB (at 31.25 MHz) 38.4 dB (at 62.5 MHz) 35.3 dB (at 100 MHz)
Power-summated near end crosstalk attenuation (PSNEXT)	62.3 dB (with 1 MHz) 53.3 dB (at 4 MHz) 48.8 dB (at 8 MHz) 47.3 dB (at 10 MHz) 44.2 dB (at 16 MHz) 42.8 dB (at 20 MHz) 41.3 dB (at 25 MHz) 39.9 dB (at 31.25 MHz) 35.4 dB (at 62.5 MHz) 32.3 dB (at 100 MHz)
Return attenuation (RL)	20 dB (with 1 MHz) 23 dB (at 4 MHz) 24.5 dB (at 8 MHz) 25 dB (at 10 MHz) 25 dB (at 16 MHz) 25 dB (at 20 MHz) 24.2 dB (at 25 MHz) 23.3 dB (at 31.25 MHz) 20.7 dB (at 62.5 MHz) 19 dB (at 100 MHz)
Shield attenuation	3.2 dB (with 1 MHz) 6.01 dB (at 4 MHz) 9.49 dB (at 10 MHz) 12.07 dB (at 16 MHz) 13.54 dB (at 20 MHz) 17.11 dB (at 31.25 MHz) 24.76 dB (at 62.5 MHz) 31.99 dB (at 100 MHz)
Halogen-free	complying with IEC 60754-1/2

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

Flame resistance	IEC 60332-1-2/IEC 60332-3-24/CM
Ambient temperature (operation)	-20 °C ... 80 °C (cable, fixed installation)
Ambient temperature (installation)	-20 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (storage/transport)	0 °C ... 60 °C

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

## Standards and regulations

Flame resistance	IEC 60332-1-2
------------------	---------------

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1523704>



**UL Listed**

Approval ID: E335024\_20210804



**cUL Listed**

Approval ID: E335024\_20210804

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 9.0	EC001855
----------	----------

# NBC-R4OC/7,5-BC6A/R4OC-GR - Patch cable



1523704

<https://www.phoenixcontact.com/us/products/1523704>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)