

1539414
<https://www.phoenixcontact.com/us/products/1539414>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Extension module, co-processor with E3940 Intel Atom® with 8 GB of RAM, Windows® 11 Pro operating system



Product description

Developed according to IEC 61850-3 (Ambient conditions)

Your advantages

- Network structure according to IEC 61850
- IEEE 1613

Commercial data

Item number	1539414
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN36
Product key	DNN511
GTIN	4067923010826
Weight per piece (including packing)	719 g
Weight per piece (excluding packing)	458 g
Country of origin	CA

FL SWITCH EP7400-MCP-W-512GB - Communication module



1539414

<https://www.phoenixcontact.com/us/products/1539414>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Extension module
Product family	Managed Switch EP7000
Basic functions	Media module for modular managed switch

System properties

Memory type	512 GByte
-------------	-----------

Functionality

Basic functions	Media module for modular managed switch
-----------------	---

Interfaces

Ethernet

Connection method	RJ45 jack
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

Mounting

Mounting type	Rack mounting
Holder system	19" rack

FL SWITCH EP7400-MCP-W-512GB - Communication module



1539414
<https://www.phoenixcontact.com/us/products/1539414>

Classifications

ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

ETIM

ETIM 9.0	EC000734
----------	----------

FL SWITCH EP7400-MCP-W-512GB - Communication module



1539414

<https://www.phoenixcontact.com/us/products/1539414>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	N,N-dimethylacetamide(CAS: 127-19-5)
	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead titanium trioxide(CAS: 12060-00-3)
	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Terphenyl, hydrogenated(CAS: 61788-32-7)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com