

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 1, power contacts: 1, control contacts: 0, Socket, Crimp connection, 830 V, 100 A, 10 mm² ... 35 mm², application: Power, without crimp contacts

Commercial data

Item number	1544119
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4067923017023
Weight per piece (including packing)	13.8 g
Weight per piece (excluding packing)	13.8 g
Customs tariff number	85389099
Country of origin	DE

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Technical data

Notes

General	For HEAVYCON housing design B6 to B48, HC-M-MHR... hinged retaining frame required, CK8,0-ED... crimp contacts (crimp contacts not supplied as standard)
General	Order crimp contacts separately

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-01
Application	Power
Number of positions	1
Connection profile	1
Number of module slots	1
No. of power contacts	1
No. of control contacts	0
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data

Connection technology

Connection technology	Crimp connection
-----------------------	------------------

Conductor connection

Conductor cross section	10 mm ² ... 35 mm ² (The cross section specification refers to the geometric cross section of the cable used)
Connection cross section AWG	8 ... 2 (The cross section specification refers to the geometric cross section of the cable used)

Dimensions

Width	34 mm
Height	60.8 mm
Length	15 mm

Mechanical characteristics

Minimum housing height	72 mm
Contact diameter	8 mm

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Electrical properties

Rated voltage (III/2) contacts	1000 V
Rated voltage (III/3)	830 V
Rated surge voltage	8 kV
Rated current	100 A

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC


Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

Standards and regulations

Testing	
Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)

Drawings



Derating diagram

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1544119>

DNV

Approval ID: TAE000037S

CSA

Approval ID: 158887

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	1000 V	100 A	- 2	-

UL Recognized

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	1000 V	100 A	- 2	-

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Classifications

ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-01-CT-F-35 - Contact insert module

1544119

<https://www.phoenixcontact.com/us/products/1544119>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com