

# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 4 mm ... 8 mm, shielding: no, connecting thread: M16 x 1.5, color: silver-gray RAL 7001

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

Item number	1424475
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DCX
GTIN	4055626372655
Weight per piece (including packing)	6.29 g
Weight per piece (excluding packing)	6.29 g
Customs tariff number	39269097
Country of origin	TR

# G-INS-M16-T68N-PNES-GY - Cable gland



1424475

<https://www.phoenixcontact.com/us/products/1424475>

## Technical data

### Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---

### Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BM-EN-01
Shielded	no
Execution of the strain relief	A

### Characteristics

Category of shock impact	2
Design, Strain relief	A

### Dimensions

Dimensional drawing	
Length	39 mm
Length of the connecting thread	8 mm
Hole diameter	16.1 mm ... 16.2 mm
Wrench size, union nut	19 mm
Wrench size, support	19 mm
Hexagon angular dimension	25 mm
Thread type connection side	M16 x 1.5
Thread pitch	1.5 mm

### Connection data

Tightening torque	2.5 Nm $\pm$ 0.5 Nm (Cap nut) 2.5 Nm (Support sleeve)
-------------------	--

### Material specifications

Color	silver grey (RAL 7001)
Flammability rating according to UL 94	V2

# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



Seal material Cable seal	CR
Material for screw connection	PA

## Cable/line

External cable diameter Cable 1	4 mm ... 8 mm
External cable diameter	4 mm ... 8 mm (for UL 514 B)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Enclosure rating (NEMA)	1
	4
	4X
	12
	13
Ambient temperature (operation)	-40 °C ... 100 °C (static)


# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



## Drawings



Dimensional drawing

# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424475>

**DNV**

Approval ID: TAE00003WX



**CSA**

Approval ID: 115116



**UL Recognized**

Approval ID: E199260

# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



## Classifications

### ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# G-INS-M16-T68N-PNES-GY - Cable gland

1424475

<https://www.phoenixcontact.com/us/products/1424475>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.055 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)