

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Pin, angled, M12-SPEEDCON, A-coding, THR and wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1438037
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEAGA
GTIN	4046356457514
Weight per piece (including packing)	12.81 g
Weight per piece (excluding packing)	9.258 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	--

### Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	A
Thread type	M12

### Insulation characteristics

Ovvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au
Material Seal	NBR
Flammability rating according to UL 94	V0

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Connection data

Conductor connection	
Connection method	THR and wave soldering
Contact connection type	Pin

### Connector

Connection 1	
Head design	Pin

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

Head cable outlet	angled
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting




1438037

<https://www.phoenixcontact.com/us/products/1438037>

## Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1438037>

UL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine					
		60 V	4 A	22	-

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-MS-5CON-L90 SH SCO - Device connector rear mounting



1438037

<https://www.phoenixcontact.com/us/products/1438037>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	088a9d62-9be1-4326-974d-682bf931b685

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)