

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 1000 V, nominal current: 17.5 A, number of connections: 2, connection method: Screw connection, Rated cross section: 1.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 1.5 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: violet

## Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Space savings and flexibility with the connection of two identical conductors
- Long-term stable connections with the use of high-quality materials
- Low self-heating due to high contact forces
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Vibration-resistant and maintenance-free conductor connection

## Commercial data

Item number	1467080
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE01
Product key	BE1111
GTIN	4063151863036
Weight per piece (including packing)	5.8 g
Weight per piece (excluding packing)	5 g
Customs tariff number	85369010
Country of origin	IN

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Technical data

### Product properties

Product type	Feed-through terminal block
Product family	UT
Area of application	Railway industry Machine building Plant engineering Process industry
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.56 W

### Connection data

Number of connections per level	2
Nominal cross section	1.5 mm <sup>2</sup>
Rated cross section AWG	16
Connection method	Screw connection
Screw thread	M2
Tightening torque	0.22 ... 0.25 Nm
Stripping length	7 mm ... 8 mm
Internal cylindrical gage	A1 B1
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Cross section AWG	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
2 conductors with same cross section, solid	0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
2 conductors with same cross section, flexible	0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.14 mm <sup>2</sup> ... 0.34 mm <sup>2</sup>
Nominal current	17.5 A
Maximum load current	17.5 A (with 1.5 mm <sup>2</sup> conductor cross-section)
Nominal voltage	1000 V

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



Nominal cross section

1.5 mm<sup>2</sup>

## Ex data

Rated data (ATEX/IECEx)

Identification	Ex II 2 GD Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3047028 D-UT 2,5/10 3022276 CLIPFIX 35-5 1204504 SZF 0-0,4X2,5
List of bridges	Plug-in bridge / FBS 2-4 / 3030116 Plug-in bridge / FBS 3-4 / 3030129 Plug-in bridge / FBS 4-4 / 3030132 Plug-in bridge / FBS 5-4 / 3030145 Plug-in bridge / FBS 10-4 / 3030158 Plug-in bridge / FBS 20-4 / 3030352
Bridge data	16.5 A (1.5 mm <sup>2</sup> )
Ex temperature increase for bridging with bridge	40 K (18,3 A / 1,5 mm <sup>2</sup> ) 690 V
- At bridging between non-adjacent terminal blocks	352 V
- At bridging between non-adjacent terminal blocks via PE terminal block	352 V
- At cut-to-length bridging	275 V
- At cut-to-length bridging with cover	275 V
Rated insulation voltage output	630 V (Permanent)

Ex level General

Rated voltage	690 V
Rated current	16.5 A (1.5 mm <sup>2</sup> )
Maximum load current	16.5 A (1.5 mm <sup>2</sup> )
Contact resistance	1.83 mΩ

Ex connection data General

Torque range	0.22 Nm ... 0.25 Nm
Nominal cross section	1.5 mm <sup>2</sup>
Rated cross section AWG	16
Connection capacity rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Connection capacity AWG	26 ... 16
Connection capacity flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Connection capacity AWG	26 ... 16
2 conductors with same cross section, solid	0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
2 conductors with the same cross-section AWG rigid	26 ... 18
2 conductors with same cross section, stranded	0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
2 conductors with the same cross-section AWG flexible	26 ... 18

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Dimensions

Width	4.15 mm
Height	48 mm
Depth	46.9 mm

## Material specifications

Color	violet (RAL 4005)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

## Mechanical properties

Mechanical data	
Open side panel	Yes

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

Mounting type	NS 35/7,5
	NS 35/15

# UT 1,5 VT - Feed-through terminal block


1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Drawings

Circuit diagram



# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1467080>

cULus Recognized				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B	600 V	15 A	30 - 14	-
C	600 V	15 A	30 - 14	-
F	1000 V	15 A	30 - 14	-
D	600 V	5 A	30 - 14	-

cCSAus				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B	600 V	15 A	30 - 14	-
C	600 V	15 A	30 - 14	-
F	1000 V	15 A	30 - 14	-
D	600 V	5 A	30 - 14	-

DNV				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Only flexible conductors	690 V	16.5 A	-	0.14 - 1.5
Only rigid conductors	690 V	16.5 A	-	0.14 - 1.5

ATEX				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Only flexible conductors	690 V	16.5 A	-	0.14 - 1.5
Only rigid conductors	690 V	16.5 A	-	0.14 - 1.5

IECEx				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Only flexible conductors	690 V	16.5 A	-	0.14 - 1.5
Only rigid conductors	690 V	16.5 A	-	0.14 - 1.5

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Only flexible conductors	690 V	16.5 A	-	0.14 - 1.5
Only rigid conductors	690 V	16.5 A	-	0.14 - 1.5



CCC

Approval ID: 2020322313000622

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Classifications

### ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

### ETIM

ETIM 9.0	EC000897
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## Accessories

Note: Applying some accessories below might limit this product.

### FBS 2-4 - Plug-in bridge

3030116

<https://www.phoenixcontact.com/us/products/3030116>

Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: red



Max. current carrying capacity: 17.5 A

### FBS 3-4 - Plug-in bridge

3030129

<https://www.phoenixcontact.com/us/products/3030129>

Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: red



Max. current carrying capacity: 17.5 A

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 4-4 - Plug-in bridge

3030132

<https://www.phoenixcontact.com/us/products/3030132>

Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: red



Max. current carrying capacity: 17.5 A

---

## FBS 5-4 - Plug-in bridge

3030145

<https://www.phoenixcontact.com/us/products/3030145>

Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: red



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 10-4 - Plug-in bridge

3030158

<https://www.phoenixcontact.com/us/products/3030158>

Plug-in bridge, pitch: 4.2 mm, number of positions: 10, color: red



Max. current carrying capacity: 17.5 A

---

## FBS 20-4 - Plug-in bridge

3030352

<https://www.phoenixcontact.com/us/products/3030352>

Plug-in bridge, pitch: 4.2 mm, number of positions: 20, color: red



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 2-4 BU - Plug-in bridge

3030117

<https://www.phoenixcontact.com/us/products/3030117>

Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: blue



Max. current carrying capacity: 17.5 A

---

## FBS 3-4 BU - Plug-in bridge

3030130

<https://www.phoenixcontact.com/us/products/3030130>

Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: blue



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 4-4 BU - Plug-in bridge

3030133

<https://www.phoenixcontact.com/us/products/3030133>

Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: blue



Max. current carrying capacity: 17.5 A

---

## FBS 5-4 BU - Plug-in bridge

3030146

<https://www.phoenixcontact.com/us/products/3030146>

Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: blue



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 10-4 BU - Plug-in bridge

3036851

<https://www.phoenixcontact.com/us/products/3036851>

Plug-in bridge, pitch: 4.2 mm, number of positions: 10, color: blue



Max. current carrying capacity: 17.5 A

---

## FBS 20-4 BU - Plug-in bridge

3030353

<https://www.phoenixcontact.com/us/products/3030353>

Plug-in bridge, pitch: 4.2 mm, number of positions: 20, color: blue



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 2-4 GY - Plug-in bridge

3030118

<https://www.phoenixcontact.com/us/products/3030118>

Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: gray



Max. current carrying capacity: 17.5 A

---

## FBS 3-4 GY - Plug-in bridge

3030131

<https://www.phoenixcontact.com/us/products/3030131>

Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: gray



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## FBS 4-4 GY - Plug-in bridge

3030134

<https://www.phoenixcontact.com/us/products/3030134>

Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: gray



Max. current carrying capacity: 17.5 A

---

## FBS 5-4 GY - Plug-in bridge

3030147

<https://www.phoenixcontact.com/us/products/3030147>

Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: gray



Max. current carrying capacity: 17.5 A

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## D-UT 2,5/10 - End cover

3047028

<https://www.phoenixcontact.com/us/products/3047028>

End cover, depth: 39.8 mm, width: 2.2 mm, height: 47 mm, color: gray



## ATP-UT - Partition plate

3047167

<https://www.phoenixcontact.com/us/products/3047167>

Partition plate, depth: 45.7 mm, width: 2.2 mm, height: 53.4 mm, color: gray



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## D-UT 2,5/10 YE - End cover

3047248

<https://www.phoenixcontact.com/us/products/3047248>

End cover, depth: 39.8 mm, width: 2.2 mm, height: 47 mm, color: yellow



---

## NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/us/products/0801733>

DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver



# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/us/products/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver-colored

---

NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/us/products/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: silver-colored

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/us/products/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: silver-colored

---

NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/us/products/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver-colored

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/us/products/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, zinc plating, Standard profile, color: silver-colored

---

NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/us/products/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, zinc plating, Standard profile, color: silver-colored

---

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/us/products/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

---

NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/us/products/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## NS 35/15 PERF 2000MM - DIN rail perforated

1201730

<https://www.phoenixcontact.com/us/products/1201730>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver-colored

---

## NS 35/15 UNPERF 2000MM - DIN rail, unperforated

1201714

<https://www.phoenixcontact.com/us/products/1201714>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver-colored

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

NS 35/15 WH PERF 2000MM - DIN rail perforated

0806602

<https://www.phoenixcontact.com/us/products/0806602>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: white

---

NS 35/15 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204135

<https://www.phoenixcontact.com/us/products/1204135>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: silver-colored

---

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

NS 35/15 AL UNPERF 2000MM - DIN rail, unperforated

1201756

<https://www.phoenixcontact.com/us/products/1201756>

DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver-colored



---

NS 35/15 ZN PERF 2000MM - DIN rail perforated

1206599

<https://www.phoenixcontact.com/us/products/1206599>

DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, zinc plating, Standard profile, color: silver-colored



# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated

1206586

<https://www.phoenixcontact.com/us/products/1206586>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, zinc plating, Standard profile, color: silver-colored

---

NS 35/15 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201895

<https://www.phoenixcontact.com/us/products/1201895>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

NS 35/15 CAP - End cap

1206573

<https://www.phoenixcontact.com/us/products/1206573>

DIN rail end piece, for DIN rail NS 35/15



---

NS 35/15-2,3 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201798

<https://www.phoenixcontact.com/us/products/1201798>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver-colored

---

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## ZB 4 :UNBEDRUCKT - Zack marker strip

0805001

<https://www.phoenixcontact.com/us/products/0805001>



Zack marker strip, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 4.2 mm

## ZB 4 CUS - Zack marker strip

0824951

<https://www.phoenixcontact.com/us/products/0824951>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 4.2 mm

# UT 1,5 VT - Feed-through terminal block




1467080

<https://www.phoenixcontact.com/us/products/1467080>

ZB 4,LGS:FORTL.ZAHLEN - Zack marker strip

0805739

<https://www.phoenixcontact.com/us/products/0805739>




Zack marker strip, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 4.2 mm

ZB 4,QR:FORTL.ZAHLEN - Zack marker strip

0805807

<https://www.phoenixcontact.com/us/products/0805807>



Zack marker strip, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 4.2 mm

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## UC-TM 4 - Marker for terminal blocks

0818111

<https://www.phoenixcontact.com/us/products/0818111>

Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 10.5 mm, text field width: 3.6 mm



## UC-TM 4 CUS - Marker for terminal blocks

0824573

<https://www.phoenixcontact.com/us/products/0824573>

Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 10.5 mm, text field width: 3.6 mm



# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## UCT-TM 4 - Marker for terminal blocks

0828732

<https://www.phoenixcontact.com/us/products/0828732>

Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 84, text field height: 10.5 mm, text field width: 3.6 mm



## UCT-TM 4 CUS - Marker for terminal blocks

0829588

<https://www.phoenixcontact.com/us/products/0829588>

Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, Number of individual labels: 84, text field height: 10.5 mm, text field width: 3.6 mm



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/us/products/0808587>



Zack Marker strip, flat, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm

## ZBF 4 CUS - Zack Marker strip, flat

0825023

<https://www.phoenixcontact.com/us/products/0825023>



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm

# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

ZBF 4,LGS:FORTL.ZAHLEN - Zack Marker strip, flat

0808626

<https://www.phoenixcontact.com/us/products/0808626>

Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm



ZBF 4,QR:FORTL.ZAHLEN - Zack Marker strip, flat

0808820

<https://www.phoenixcontact.com/us/products/0808820>

Zack Marker strip, flat, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.2 mm, text field width: 4.2 mm



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

ZBF 4,LGS:GERADE ZAHLEN - Zack Marker strip, flat

0810818

<https://www.phoenixcontact.com/us/products/0810818>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive even numbers 2 ... 20, 22 ... 40, etc. up to 82 ... 100, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.15 mm, text field width: 4.15 mm

ZBF 4,LGS:UNGERADE ZAHLEN - Zack Marker strip, flat

0810850

<https://www.phoenixcontact.com/us/products/0810850>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: Odd numbers 1 - 19, 21 - 39, etc. up to 81 - 99, mounting type: latching, for terminal block width: 4 mm, Number of individual labels: 10, text field height: 5.15 mm, text field width: 4.15 mm

# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/us/products/0818166>

Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 5.1 mm, text field width: 3.6 mm



## UC-TMF 4 CUS - Marker for terminal blocks

0824630

<https://www.phoenixcontact.com/us/products/0824630>

Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, Number of individual labels: 120, text field height: 5.1 mm, text field width: 3.6 mm



# UT 1,5 VT - Feed-through terminal block

1467080

<https://www.phoenixcontact.com/us/products/1467080>



## UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/us/products/0828742>

Marker for terminal blocks, Sheet, white, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 4.2 mm, Number of individual labels: 90, text field height: 4.7 mm, text field width: 3.4 mm



## UCT-TMF 4 CUS - Marker for terminal blocks

0829651

<https://www.phoenixcontact.com/us/products/0829651>

Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, Number of individual labels: 90, text field height: 4.7 mm, text field width: 3.4 mm



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## PAI-4 - Test adapter

3030925

<https://www.phoenixcontact.com/us/products/3030925>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: gray

## PS-4 - Test plug

3030970

<https://www.phoenixcontact.com/us/products/3030970>

Test plug, Modular test plug, number of positions: 1, color: red



# UT 1,5 VT - Feed-through terminal block



1467080

<https://www.phoenixcontact.com/us/products/1467080>

## DP PS-4 - Spacer plate

3036712

<https://www.phoenixcontact.com/us/products/3036712>



Spacer plate, depth: 29 mm, width: 4.2 mm, height: 22.4 mm, number of positions: 1, color: red

## SZF 0-0,4X2,5 - Screwdriver

1204504

<https://www.phoenixcontact.com/us/products/1204504>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)