

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Sensor/actuator cable, shielded, PVC, black RAL 9005, 8-wire, color single wire:
white, brown, green, yellow, gray, pink, blue, red, cable length: 100 m



Commercial data

Item number	1550708
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4046356170512
Weight per piece (including packing)	8,950 g
Weight per piece (excluding packing)	6,608 g
Customs tariff number	85444995
Country of origin	DE

Technical data

Product properties

Product type	Cable by the meter
Application	Connector
Number of positions	8
Shielded	yes

Cable/line

Cable length	100 m
--------------	-------

PVC black [PVC]

Dimensional drawing



Note	The cable is not suitable for use with drag chains.
Cable weight	85 kg/km
UL AWM Style	2517
Number of positions	8
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	8x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	7.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC
Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.38 mm (Conductor insulation, signal line)
	≥ 0.76 mm (Outer cable sheath)
Overall twist	8 wires around filler to the core, twisted in with additional Cu litz in the wire outer godet
Optical shield covering	85 %
Max. conductor resistance	≤ 78 Ω/km
Insulation resistance	≥ 10 GΩ*km

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable

1550708

<https://www.phoenixcontact.com/us/products/1550708>



Nominal voltage, cable	300 V
Test voltage	3000 V
Smallest bending radius, fixed installation	38.5 mm
Smallest bending radius, movable installation	77 mm
Flame resistance	According to UL 758/1581 (Cable Flame) According to DIN EN 60332-1-2 (60 s)
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 80°C
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-25 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C ... 80 °C (Cable, flexible installation)

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable



1550708

<https://www.phoenixcontact.com/us/products/1550708>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1550708>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	30 V	2 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine	30 V	2 A	-	-



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable

1550708

<https://www.phoenixcontact.com/us/products/1550708>



Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-8P-100,0-PVC/SH-0,25 - Sensor/actuator cable

1550708

<https://www.phoenixcontact.com/us/products/1550708>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	71.767 kg CO2e
---------	----------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com