

HC-B 16-I-CT-F-32 - Contact insert

1584923

<https://www.phoenixcontact.com/us/products/1584923>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 16+PE, size: B16, Socket, Crimp connection, 500 V, 16 A, 0.5 mm² ... 4 mm²

Your advantages

- For fast coding with plastic profile

- Shock and vibration-resistant in accordance with DIN EN 61373

Commercial data

Item number	1584923
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABC
GTIN	4046356156134
Weight per piece (including packing)	59.6 g
Weight per piece (excluding packing)	59.6 g
Customs tariff number	85366990
Country of origin	CN

HC-B 16-I-CT-F-32 - Contact insert



1584923

<https://www.phoenixcontact.com/us/products/1584923>

Technical data

Notes

General	For HEAVYCON ADVANCE housing of B16 type and HEAVYCON housing of B16/B32 type, crimp contacts CK 2,5-ED (crimp contacts not included in the scope of supply).
General	Connectors may be operated only when there is no load/voltage.

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
	Remove the crimp contact using a screwdriver. The opening for the screwdriver is next to the opening where the conductor is inserted.

Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-B
Type	B16
	B32
Number of positions	16
Connection profile	16+PE
Contact numbering	17 - 32
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	34 mm
Height	34.6 mm
Length	84 mm
Drill hole distance, horizontal	77.5 mm

Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

Connection data

Connection technology

HC-B 16-I-CT-F-32 - Contact insert

1584923

<https://www.phoenixcontact.com/us/products/1584923>



Connection technology	Crimp connection
Connection in acc. with standard	IEC / EN

Conductor connection

Conductor cross section	0.5 mm ² ... 4 mm ²
Connection cross section AWG	20 ... 12
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection) 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
Stripping length of the individual wire	7.5 mm

Electrical properties

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	16 A
SCCR	5 kA (UL 2237)

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC
Standards/regulations	PC

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)

Standards and regulations

Constructional and testing regulations	DIN EN 61984 DIN EN 60664 IEC 60352
Tests	DIN EN 61984 DIN EN 60664 IEC 60352

Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---

HC-B 16-I-CT-F-32 - Contact insert




1584923

<https://www.phoenixcontact.com/us/products/1584923>


Drawings

Dimensional drawing



Female insert

Dimensional drawing



Mounting cutout when used without housing


HC-B 16-I-CT-F-32 - Contact insert



1584923


<https://www.phoenixcontact.com/us/products/1584923>

Schematic diagram



Connector pin assignment, connection side

Diagram



Derating diagram

HC-B 16-I-CT-F-32 - Contact insert

1584923

<https://www.phoenixcontact.com/us/products/1584923>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1584923>

DNV

Approval ID: TAE000037S

 CSA	Approval ID: 013631_6233_01	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		600 V	20 A	20 - 12	-

 cULus Recognized	Approval ID: E468743	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		600 V	13 A	-	-

 cULus Recognized	Approval ID: E468743	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		600 V	14 A	-	-

HC-B 16-I-CT-F-32 - Contact insert

1584923

<https://www.phoenixcontact.com/us/products/1584923>



Classifications

ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

HC-B 16-I-CT-F-32 - Contact insert

1584923

<https://www.phoenixcontact.com/us/products/1584923>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com