

Q 0,34/4IDC/16-16KU-KU BK - Conductor connector



1641879

<https://www.phoenixcontact.com/us/products/1641879>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor connector, connection method: IDC connection, 0.14 mm² ... 0.34 mm², 125 V, 5 A, black, coding: no, external cable diameter: 3.5 mm ... 6 mm

Your advantages

- Innovative and time saving - QUICKON fast connection for time saving of up to 80 % for on-site connection
- Safer connection with mechanical coding to protect against mismatching, and touch-proof protection in accordance with DIN EN 0105
- Easy and safe - with the cable connector, you can repair or extend cables quickly, in combination with the connector as well as the coupling connection

Commercial data

Item number	1641879
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF50
Product key	AF6HCA
GTIN	4017918925185
Weight per piece (including packing)	14.3 g
Weight per piece (excluding packing)	14.4 g
Customs tariff number	85366990
Country of origin	DE

Technical data


Product properties

Product type	Cable connector
Number of positions	4
Position marking	1, 2, 3, 4
Number of connections	4
Number of connections per position	1
Coding	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	16.3 mm
Height	16.3 mm
Length	70 mm
Diameter	16.3 mm

Connection data

Connection technology

Frequency of connections between conductors of the same cross section	max. 10
---	---------

Conductor connection

Tightening torque	0.8 Nm
Tightening torque Union nut	0.8 Nm

Electrical properties

Rated surge voltage (II/2)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (III/3)	2.5 kV
Rated current	5 A
Contact resistance	≤ 5 mΩ
rated voltage (II/2)	320 V
rated voltage (III/2)	200 V
Rated voltage (III/3)	125 V
Insulation resistance	≥ 100 MΩ

Q 0,34/4IDC/16-16KU-KU BK - Conductor connector

1641879

<https://www.phoenixcontact.com/us/products/1641879>



Nominal voltage U_N	125 V AC
	125 V DC
Nominal current I_N	5 A

Material specifications

Color	black (RAL 9005)
Material Housing	PA
Material Contact	Steel
Material Contact surface	Sn
Flammability rating according to UL 94	V0
Material wire insulation	PVC/PE/TPE/rubber

Cable/line

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 class 1 to 6/min. 0.15 mm
External cable diameter	3.5 mm ... 6 mm
Wire diameter including insulation	0.7 mm ... 1.6 mm
Position marking	1, 2, 3, 4
Material wire insulation	PVC / PE

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Impact strength	IK06
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 80 °C
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

Q 0,34/4IDC/16-16KU-KU BK - Conductor connector




1641879


<https://www.phoenixcontact.com/us/products/1641879>

Drawings

Dimensional drawing



Functional drawing



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1641879>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: RU C-DE.A*30.B.01102

Classifications

ECLASS

ECLASS-13.0	27440605
ECLASS-15.0	27440605

ETIM

ETIM 9.0	EC002560
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.152 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com