

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, nominal current: 8 A, rated voltage (III/2): 160 V, nominal cross section: 1 mm<sup>2</sup>, number of potentials: 6, number of rows: 1, number of positions per row: 6, product range: MKDS 1/...SMD, pitch: 3.81 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, mounting: SMD soldering, conductor/PCB connection direction: 0 °, color: black, Pin layout: Linear pad geometry, number of solder pins per potential: 1, type of packaging: Tube magazine

Your advantages

- Well-known connection principle allows worldwide use
- Low temperature rise, thanks to maximum contact force
- Allows connection of two conductors
- Extremely small design for the respective conductor cross-section
- Designed for integration into the SMT soldering process

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1727272                        |
| Packing unit                         | 17 pc                          |
| Minimum order quantity               | 17 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA12                           |
| Product key                          | AALHAB                         |
| GTIN                                 | 4017918025649                  |
| Weight per piece (including packing) | 6.71 g                         |
| Weight per piece (excluding packing) | 6.288 g                        |
| Customs tariff number                | 85369010                       |
| Country of origin                    | PL                             |

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

## Technical data

### Product properties

|                           |                                |
|---------------------------|--------------------------------|
| Product type              | Printed circuit board terminal |
| Product family            | MKDS 1/..-SMD                  |
| Product line              | COMBICON Terminals S           |
| Type                      | PC termination block           |
| Number of positions       | 6                              |
| Pitch                     | 3.81 mm                        |
| Number of connections     | 6                              |
| Number of rows            | 1                              |
| Number of potentials      | 6                              |
| Pin layout                | Linear pad geometry            |
| Solder pins per potential | 1                              |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 8 A    |
| Nominal voltage $U_N$       | 160 V  |
| Rated voltage (III/3)       | 160 V  |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 250 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Connection data

#### Connection technology

|                       |                      |
|-----------------------|----------------------|
| Type                  | PC termination block |
| Nominal cross section | 1 mm <sup>2</sup>    |

#### Conductor connection

|                                                                       |                                              |
|-----------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                     | Screw connection with tension sleeve         |
| Conductor cross-section rigid                                         | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible                                      | 0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |
| Conductor cross-section AWG                                           | 26 ... 16                                    |
| Conductor cross-section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| 2 conductors with same cross section, solid                           | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible                        | 0.14 mm <sup>2</sup> ... 0.2 mm <sup>2</sup> |
| Stripping length                                                      | 5 mm                                         |
| Drive form screw head                                                 | Slotted (L)                                  |

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

|                   |                     |
|-------------------|---------------------|
| Tightening torque | 0.22 Nm ... 0.25 Nm |
|-------------------|---------------------|

## Mounting

|               |                     |
|---------------|---------------------|
| Mounting type | SMD soldering       |
| Pin layout    | Linear pad geometry |

## Material specifications

### Material data - contact

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Surface characteristics                     | Tin-plated                                                                       |
| Metal surface terminal point (top layer)    | Tin (5 - 7 µm Sn)                                                                |
| Metal surface terminal point (middle layer) | Nickel (2 - 3 µm Ni)                                                             |
| Metal surface soldering area (top layer)    | Tin (5 - 7 µm Sn)                                                                |
| Metal surface soldering area (middle layer) | Nickel (2 - 3 µm Ni)                                                             |


### Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | black (9005) |
| Insulating material                                               | PA           |
| Insulating material group                                         | IIIa         |
| CTI according to IEC 60112                                        | 250          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Notes

|                     |                                                                                                                                               |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application | Pick and place pads may protrude beyond the components. The PCB layout must ensure that collisions are avoided when components are assembled. |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 3.81 mm                                                                              |
| Width [w]           | 30.43 mm                                                                             |
| Height [h]          | 9.2 mm                                                                               |
| Length [l]          | 9.3 mm                                                                               |

### PCB design

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

|              |              |
|--------------|--------------|
| Pad geometry | 1.5 x 2.5 mm |
|--------------|--------------|

## Mechanical tests

### Test for conductor damage and slackening

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Pull-out test

|                                                                             |                                          |
|-----------------------------------------------------------------------------|------------------------------------------|
| Specification                                                               | IEC 60999-1:1999-11                      |
| Conductor cross-section/conductor type/tractive force setpoint/actual value | 0.14 mm <sup>2</sup> / solid / > 10 N    |
|                                                                             | 0.14 mm <sup>2</sup> / flexible / > 10 N |
|                                                                             | 1.5 mm <sup>2</sup> / solid / > 40 N     |
|                                                                             | 1 mm <sup>2</sup> / flexible / > 35 N    |

## Electrical tests

### Temperature-rise test

|                                   |                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| Specification                     | IEC 60947-7-4:2019-01                                                                                                          |
| Requirement temperature-rise test | The sum of ambient temperature and temperature rise of the PCB terminal block shall not exceed the upper limiting temperature. |

### Short-time withstand current

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                                                        |                                               |
|--------------------------------------------------------|-----------------------------------------------|
| Specification                                          | IEC 60947-1:2007-06 + A1:2010-12 + A2:2014-09 |
| Insulating material group                              | IIIa                                          |
| Comparative tracking index (IEC 60112)                 | CTI 250                                       |
| Rated insulation voltage (III/3)                       | 160 V                                         |
| Rated surge voltage (III/3)                            | 2.5 kV                                        |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm                                        |
| minimum creepage distance (III/3)                      | 2.5 mm                                        |
| Rated insulation voltage (III/2)                       | 160 V                                         |
| Rated surge voltage (III/2)                            | 2.5 kV                                        |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm                                        |
| minimum creepage distance (III/2)                      | 1.6 mm                                        |
| Rated insulation voltage (II/2)                        | 250 V                                         |
| Rated surge voltage (II/2)                             | 2.5 kV                                        |
| minimum clearance value - non-homogenous field (II/2)  | 1.5 mm                                        |
| minimum creepage distance (II/2)                       | 2.5 mm                                        |

## Environmental and real-life conditions

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

## Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

## Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-10:2013-04 |
| Temperature      | 850 °C                 |
| Time of exposure | 5 s                    |

## Aging

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

## Ambient conditions


|                                         |                                                                               |
|-----------------------------------------|-------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 105 °C (Depending on the current carrying capacity/derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                                              |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                                                 |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                                              |

## Packaging specifications


|                   |               |
|-------------------|---------------|
| Type of packaging | Tube magazine |
|-------------------|---------------|

## Drawings

Dimensional drawing



Diagram



Type: MKDS 1/...-3,81 SMD BK


# MKDS 1/ 6-3,81 SMD BK - PCB terminal block

1727272

<https://www.phoenixcontact.com/us/products/1727272>



Drilling plan/solder pad geometry



# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1727272>

|  <b>cULus Recognized</b><br>Approval ID: E60425-19770427 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                         |                       |                       |                   |                             |
| Only flexible conductors                                                                                                                  | 300 V                 | 13.5 A                | 30 - 16           | -                           |
| Standard                                                                                                                                  | 300 V                 | 10 A                  | 30 - 16           | -                           |
| D                                                                                                                                         |                       |                       |                   |                             |
| Only flexible conductors                                                                                                                  | 150 V                 | 13.5 A                | 30 - 16           | -                           |
| Standard                                                                                                                                  | 300 V                 | 10 A                  | 30 - 16           | -                           |

|  <b>VDE approval of drawings</b><br>Approval ID: 40055394 |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                              | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                        |                       |                       |                   |                             |
|                                                                                                                                              | 200 V                 | 17.5 A                | -                 | 0.2 - 1.5                   |

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460101 |
| ECLASS-15.0 | 27460101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002643 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MKDS 1/ 6-3,81 SMD BK - PCB terminal block



1727272

<https://www.phoenixcontact.com/us/products/1727272>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)