

PV-1P-500,0/S02-4,0 - Cable reel

1787700

<https://www.phoenixcontact.com/us/products/1787700>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable reel, Range of articles: SUNCLIX, number of positions: 1, cable length: 500000



Commercial data

Item number	1787700
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABLBDX
GTIN	4046356609395
Weight per piece (including packing)	58.31 g
Weight per piece (excluding packing)	58.31 g
Country of origin	DE

PV-1P-500,0/S02-4,0 - Cable reel

1787700

<https://www.phoenixcontact.com/us/products/1787700>



Technical data

Product properties

Number of positions	1
Shielded	no

Electrical properties

Nominal current I_N	≤ 55 A (up to +60 °C)
-----------------------	----------------------------

Dimensions

Length	500 m
--------	-------

Material specifications

Outer sheath, material	PE-X
Conductor material	Tin-plated Cu litz wires

Cable/line

Cable length	500 m
--------------	-------

PV1-F cables [S02]

Shielded	no
Cable weight	58 kg/km
Cable type	PV1-F cables
Cable type (abbreviation)	S02
External cable diameter	5.20 mm ± 0.2 mm
Outer sheath, material	PE-X
External sheath, color	black-gray RAL 7021
Material, inner sheath	PE-X
Conductor structure, voltage supply	56x 0.30 mm
AWG power supply	12
Thickness, insulation	≥ 0.50 mm (Inner sheath)
Cable resistance	5 Ω /km (at 20 °C)
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	40 mm
Ambient temperature (operation)	-40 °C ... 90 °C
	-40 °C ... 90 °C
	-40 °C ... 90 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 90 °C
	to 120 °C (maximum permissible temperature at the conductor)
	to 200 °C (permissible short-circuit temperature - maximum of 5 s)

PV-1P-500,0/S02-4,0 - Cable reel

1787700

<https://www.phoenixcontact.com/us/products/1787700>



Standards and regulations

Flame resistance	IEC 60332-1-2
Other resistance	Resistance to acids and alkalis
	Resistant to salt water
	Resistant to ozone

PV-1P-500,0/S02-4,0 - Cable reel

1787700

<https://www.phoenixcontact.com/us/products/1787700>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com