


# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561  
<https://www.phoenixcontact.com/us/products/1793561>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 35 mm<sup>2</sup>, color: green, nominal current: 125 A, rated voltage (III/2): 1000 V, contact surface: Ag, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: IPCV 35 HC/...-GF, pitch: 15 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 4.6 mm, number of solder pins per potential: 3, plug-in system: COMBICON PC 35, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting method: Threaded flange, type of packaging: packed in cardboard

## Your advantages

- Well-known mounting principle allows worldwide use
- Inverted header with socket contacts for touch-proof device outputs or PCB/PCB connections
- Double flange for space-optimized screw connection on the housing panel and with the connector
- Integrated double steel spring provides additional safety in the event of temperature and power fluctuations

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1793561                        |
| Packing unit                         | 25 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA05                           |
| Product key                          | AAESFA                         |
| GTIN                                 | 4046356621274                  |
| Weight per piece (including packing) | 91.352 g                       |
| Weight per piece (excluding packing) | 84.05 g                        |
| Customs tariff number                | 85366930                       |
| Country of origin                    | PL                             |

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Technical data

### Product properties

|                           |                        |
|---------------------------|------------------------|
| Product type              | PCB headers            |
| Product family            | IPCV 35 HC/...-GF      |
| Product line              | COMBICON Connectors XL |
| Type                      | Headers                |
| Number of positions       | 3                      |
| Pitch                     | 15 mm                  |
| Number of connections     | 3                      |
| Number of rows            | 1                      |
| Number of potentials      | 3                      |
| Mounting type             | Threaded flange        |
| Pin layout                | Linear pinning         |
| Solder pins per potential | 3                      |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 125 A  |
| Nominal voltage $U_N$       | 1000 V |
| Contact resistance          | 0.1 mΩ |
| Rated voltage (III/3)       | 1000 V |
| Rated surge voltage (III/3) | 8 kV   |
| Rated voltage (III/2)       | 1000 V |
| Rated surge voltage (III/2) | 8 kV   |
| Rated voltage (II/2)        | 1000 V |
| Rated surge voltage (II/2)  | 8 kV   |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Wave soldering |
| Pin layout    | Linear pinning |

#### Flange

|                   |        |
|-------------------|--------|
| Tightening torque | 0.8 Nm |
|-------------------|--------|

#### Attachment to feed-through panel

|                   |                      |
|-------------------|----------------------|
| Tightening torque | 1 Nm                 |
| Screw             | 1700368 DFK-PC 35 SS |

#### Attachment on the PCB

|                   |                      |
|-------------------|----------------------|
| Tightening torque | 1 Nm                 |
| Screw             | 1700368 DFK-PC 35 SS |

### Material specifications

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Material data - contact

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Metal surface contact area (top layer)      | Silver (4 - 8 µm Ag)                                                             |
| Metal surface soldering area (top layer)    | Tin (3 - 5 µm Sn)                                                                |
| Metal surface soldering area (middle layer) | Nickel (1.3 - 3 µm Ni)                                                           |


## Material data - housing

|                                        |              |
|----------------------------------------|--------------|
| Color (Housing)                        | green (6021) |
| Insulating material                    | PBT          |
| Insulating material group              | IIIa         |
| CTI according to IEC 60112             | ≥175 < 400   |
| Flammability rating according to UL 94 | V0           |

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 15 mm                                                                                |
| Width [w]             | 69.4 mm                                                                              |
| Height [h]            | 49.5 mm                                                                              |
| Length [l]            | 28.5 mm                                                                              |
| Installed height      | 44.9 mm                                                                              |
| Solder pin length [P] | 4.6 mm                                                                               |
| Pin dimensions        | 2.4 x 2.5 mm                                                                         |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 3.6 mm |
|---------------|--------|

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Contact holder in insert

|                                                |                        |
|------------------------------------------------|------------------------|
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 50          |
| Insertion strength per pos. approx. | 14 N        |
| Withdraw strength per pos. approx.  | 7 N         |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 6                     |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI ≥175 to <400    |
| Rated insulation voltage (III/3)                       | 1000 V              |
| Rated surge voltage (III/3)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/3) | 8 mm                |
| minimum creepage distance (III/3)                      | 16 mm               |
| Rated insulation voltage (III/2)                       | 1000 V              |
| Rated surge voltage (III/2)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/2) | 8 mm                |
| minimum creepage distance (III/2)                      | 10 mm               |
| Rated insulation voltage (II/2)                        | 1000 V              |
| Rated surge voltage (II/2)                             | 8 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 8 mm                |
| minimum creepage distance (II/2)                       | 10 mm               |

## Environmental and real-life conditions

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

## Durability test

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level       | 9.8 kV                |
| Contact resistance $R_1$                     | 0.1 mΩ                |
| Contact resistance $R_2$                     | 0.1 mΩ                |
| Insertion/withdrawal cycles                  | 50                    |
| Insulation resistance, neighboring positions | > 5 MΩ                |

## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 4.26 kV                                                                   |

## Shocks

|                 |                                   |
|-----------------|-----------------------------------|
| Specification   | IEC 60068-2-27:2008-02            |
| Pulse shape     | Semi-sinusoidal                   |
| Acceleration    | 30g                               |
| Shock duration  | 18 ms                             |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

## Ambient conditions


|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications


|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

## Drawings

Dimensional drawing



Diagram



Type: IPC 35 HC/...-STF-15,00 with IPCV 35 HC/...-GF-15,00

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1793561>

| <div> <b>UL Recognized</b><br/>Approval ID: E60425-20101007</div> |                       |                       |                   |                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                                  |                       |                       |                   |                             |
|                                                                                                                                                    | 600 V                 | 115 A                 | -                 | -                           |
| C                                                                                                                                                  |                       |                       |                   |                             |
|                                                                                                                                                    | 600 V                 | 115 A                 | -                 | -                           |

| <div> <b>VDE report with production monitoring</b><br/>Approval ID: 40039053</div> |                       |                       |                   |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                                                     | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                                               |                       |                       |                   |                             |
|                                                                                                                                                                     | 1000 V                | 125 A                 | -                 | -                           |

# IPCV 35 HC/ 3-GF-15,00 - PCB header



1793561

<https://www.phoenixcontact.com/us/products/1793561>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 0.493 kg CO2e                            |