

# FLK 16/14/DV-IN/ 50 - Cable

2304393

<https://www.phoenixcontact.com/us/products/2304393>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Round cable set; controller: Emerson Delta V; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 0.5 m



## Your advantages

- The DeltaV system can be used to install the process wiring via "mass termination blocks" (MTBs) using flat-ribbon cable plugs
- For digital modules with 16-pos. MTB for connection to PLC-INTERFACE

## Commercial data

Item number	2304393
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK221K
GTIN	4017918933043
Weight per piece (including packing)	42.1 g
Weight per piece (excluding packing)	42.1 g
Customs tariff number	85444290
Country of origin	DE

# FLK 16/14/DV-IN/ 50 - Cable

2304393

<https://www.phoenixcontact.com/us/products/2304393>



## Technical data

### Product properties

Product type	System cable
Insulation characteristics: Air clearances and creepage distances	
Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

### Electrical properties

Operating voltage (AC)	≤ 25 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A
Current (Per path, 70°C)	≤ 0.6 A

#### Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

#### Supported controller EMERSON DeltaV

Suitable I/O card	VE4001S2T1B3
	VE4001S2T2B3

### Cable/line

Cable length	0.5 m
16X0.14 [PVC]	
UL AWM Style	2464/1061
Number of positions	16
Shielded	no
Cable type	16X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26

# FLK 16/14/DV-IN/ 50 - Cable



2304393

<https://www.phoenixcontact.com/us/products/2304393>

Conductor cross section	16x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	6.80 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	58 mm
Smallest bending radius, movable installation	108 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Color code: Single-core wire

black	IDC/FLK16 (1) = IDC/FLK14 (1)
brown	IDC/FLK16 (2) = IDC/FLK14 (9)
red	IDC/FLK16 (3) = IDC/FLK14 (2)
orange	IDC/FLK16 (4) = IDC/FLK14 (9)
yellow	IDC/FLK16 (5) = IDC/FLK14 (3)
green	IDC/FLK16 (6) = IDC/FLK14 (9)
blue	IDC/FLK16 (7) = IDC/FLK14 (4)
violet	IDC/FLK16 (8) = IDC/FLK14 (11)
gray	IDC/FLK16 (9) = IDC/FLK14 (5)
white	IDC/FLK16 (10) = IDC/FLK14 (11)
white-black	IDC/FLK16 (11) = IDC/FLK14 (6)
white-brown	IDC/FLK16 (12) = IDC/FLK14 (11)
white-red	IDC/FLK16 (13) = IDC/FLK14 (7)
white-orange	IDC/FLK16 (14) = IDC/FLK14 (13)
white-yellow	IDC/FLK16 (15) = IDC/FLK14 (8)
white-green	IDC/FLK16 (16) = IDC/FLK14 (13)

## Connection data

### Field level

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1

# FLK 16/14/DV-IN/ 50 - Cable

2304393

<https://www.phoenixcontact.com/us/products/2304393>



Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

## Controller level

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	16
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLK 16/14/DV-IN/ 50 - Cable




2304393

<https://www.phoenixcontact.com/us/products/2304393>

## Drawings

Diagram



Maximum permissible current per path in uncoiled state

# FLK 16/14/DV-IN/ 50 - Cable

2304393

<https://www.phoenixcontact.com/us/products/2304393>



## Classifications

### UNSPSC

UNSPSC 21.0

26121620

# FLK 16/14/DV-IN/ 50 - Cable

2304393

<https://www.phoenixcontact.com/us/products/2304393>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)