

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel, 30.7 cm / 12.1"-TFT display (Analog resistive (GFG)), 800 x 600 pixel(s) (SVGA), 16.7 million colors, Arm® Cortex®-A8, 1000 MHz, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, TSvisIT, DualCAN.

Commercial data

Item number	2401627
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCBBE
GTIN	4055626296869
Weight per piece (including packing)	2,750 g
Weight per piece (excluding packing)	2,750 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
Application	Rugged

Computer data

Processor	Arm® Cortex®-A8, 1000 MHz
Operating system	Windows® Embedded Compact 7
RAM	512 MB LPDDR SDRAM
	1 MB SRAM
Data storage system	NAND-Flash, 1 GB
Slots	1x SD
Optional keys	without

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	Analog resistive (GFG)
Display lighting type	LED
Brightness	360 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	65.00 °
Reading angle bottom	75.00 °

Interfaces

Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	DualCAN

System properties

User software	TSvisIT
---------------	---------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.6 A

Real-time clock

Realtime clock	Yes
----------------	-----

Mounting

Mounting type	Bolt fixing
---------------	-------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	-30 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	20 % ... 85 % (On the rear)
	5 % ... 95 % (Front)

Dimensions

External dimensions

Width / Height / Depth	359 mm / 280 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	323 mm / 244 mm / 58 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com