

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Industrial LTE 4G router, European version, fallback to 3G UMTS/HSPA and 2G GPRS/EDGE, 2 Ethernet interfaces, firewall, NAT, 2x SMA-F antenna socket, SMS and e-mail transmission, 2 digital inputs, 1 digital output

## Product description

The **TC ROUTER** for cellular communication implements high-performance data links of up to 150 Mbps via mobile 4G LTE networks. This enables you to establish a mobile broadband connection for highly flexible site networking even in places where a wired Internet connection is not available. These connections can be used to transmit sensitive data securely over mobile networks.

## Your advantages

- Industrial 4G cellular router (LTE)
- Fallback to 3G (UMTS/HSPA) and 2G (GPRS/EDGE)
- Cellular high-speed Internet connection up to 150 Mbps
- Networking of Ethernet end devices via the cellular network
- Ethernet SMS gateway for easy alerting
- Stateful inspection firewall for dynamic filtering
- NAT table and port forwarding for direct remote access to an end device
- Two switching inputs and one switching output
- Configuration via web-based management or microSD card
- Two local Ethernet connections
- Switchable energy-saving mode
- Integrated logbook
- Connection monitoring
- Extended temperature range of -40 °C ... +70 °C

## Commercial data

Item number	2702530
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC422
GTIN	4055626212814
Weight per piece (including packing)	357.2 g
Weight per piece (excluding packing)	240 g
Country of origin	DE

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



## Technical data

### Product properties

Product type	Cellular router
MTTF	383 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	184 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	78 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)

### Security functions

Filtering	IP, port, protocol
Firewall rules	Stateful inspection firewall

### Electrical properties

Electrical isolation	VCC // LTE // Ethernet // PE
Mains type	Cellular communication

### Supply

Supply voltage range	10 V DC ... 30 V DC (Via pluggable Push-in terminal block)
Typical current consumption	< 200 mA (24 V DC)
	65 mA (With activated energy-saving mode)

### Max. current consumption

1.7 A

### Function

Management	Web-based management, SNMP
------------	----------------------------

### Input data

#### Digital

Description of the input	Digital input
Number of inputs	2
Voltage input signal	10 V DC ... 30 V DC
Switching level "1" signal	10 V DC ... 30 V DC

### Output data

#### Signal

Output name	Digital output
Number of outputs	1
Voltage output signal	10 V DC ... 30 V DC (depending on the operating voltage)
Current output signal	≤ 50 mA (Not short-circuit proof)

### Connection data

#### Supply

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Connection method	Push-in spring connection
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
Conductor cross-section, flexible	0.14 mm <sup>2</sup> ... 1.50 mm <sup>2</sup>
Conductor cross-section, rigid	0.14 mm <sup>2</sup> ... 1.50 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 16
Stripping length	9.00 mm

## Interfaces

Signal	Ethernet
Web server	yes

Data: Ethernet interface, 10/100Base-T(X) in accordance with IEEE 802.3

Serial transmission speed	10/100 Mbps, auto negotiation
Connection method	RJ45 jack, shielded
No. of channels	2
Transmission length	100 m (shielded twisted pair)
Protocols supported	TCP/IP, UDP/IP, FTP, HTTP(S)
Auxiliary protocols	ARP, DHCP, PING (ICMP), SNMP V1/V2, SMTP(S), NTP, SSL/TLS, STARTTLS

## Wireless

Interface description	GSM / GPRS / EDGE / UMTS / HSPA / LTE (FDD)
Frequency range	800 MHz (LTE B20)
	850 MHz (LTE B5)
	900 MHz (LTE B8)
	1700 MHz (LTE B4)
	1800 MHz (LTE B3)
	1900 MHz (LTE B2)
	2100 MHz (LTE B1)
	2600 MHz (LTE B7)
	850 MHz (UMTS/HSPA B5)
	900 MHz (UMTS/HSPA B8)
	1900 MHz (UMTS/HSPA B2)
	2100 MHz (UMTS/HSPA B1)
	850 MHz (2 W (EGSM))
	900 MHz (2 W (EGSM))
	1800 MHz (1 W (EGSM))
	1900 MHz (1 W (EGSM))
Data rate	≤ 150 Mbps (LTE, DL)
	≤ 50 Mbps (LTE, UL)
Antenna	50 Ω impedance SMA antenna socket
Antenna connection method	SMA (female)
SIM Interface	1.8 volt, 3 volt

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



GPRS	Class 12, Class B
	CS1 ... CS4
EDGE	Multislot Class 10
UMTS	HSPA 3GPP R9
LTE	CAT4
Country support	Europe

## Dimensions

Dimensional drawing	
Width	45 mm
Height	130 mm
Depth	127 mm

## Material specifications

Color (Upper housing part)	light gray (RAL 7035)
Material (Housing)	Plastic

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (Maximum transmission power 5 dBm)
	-40 °C ... 60 °C (Maximum transmission power 23 dBm)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

## Approvals

CE	
Certificate	CE-compliant

Corrosive gas test	
Identification	ISA-S71.04-1985 G3 Harsh Group A

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



## EMC data

Electromagnetic compatibility	Conformance with RED Directive 2014/53/EU
Noise immunity	EN 61000-6-2
<b>Electrostatic discharge</b>	
Standards/regulations	EN 61000-4-2
<b>Electrostatic discharge</b>	
Contact discharge	± 6 kV (Test Level 3)
Discharge in air	± 8 kV (Test Level 3)
Comments	Criterion B
<b>Electromagnetic HF field</b>	
Standards/regulations	EN 61000-4-3
<b>Electromagnetic HF field</b>	
Frequency range	80 MHz ... 3 GHz (Test Level 3)
Field intensity	10 V/m
Comments	Criterion A
<b>Fast transients (burst)</b>	
Standards/regulations	EN 61000-4-4
<b>Fast transients (burst)</b>	
Input	± 2 kV (Test Level 3)
Signal	± 2 kV (Ethernet)
Comments	Criterion B
<b>Surge current load (surge)</b>	
Standards/regulations	EN 61000-4-5
<b>Surge current load (surge)</b>	
Input	± 0.5 kV (symmetrical)
	± 1 kV (asymmetrical)
Signal	± 1 kV (Data line, asymmetrical)
Comments	Criterion B
<b>Conducted interference</b>	
Standards/regulations	EN 61000-4-6
<b>Conducted interference</b>	
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V
<b>Emitted interference</b>	
Radio interference voltage in acc. with EN 55011	Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	Class B, area of application: Industry and residential

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



## Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# TC ROUTER 2002T-4G - Router


2702530

<https://www.phoenixcontact.com/us/products/2702530>



## Drawings

Dimensional drawing




# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Connection diagram



Switching inputs


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Front view


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Connect the antenna


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Remove SIM card holder


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Insert the SIM card


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Device connections


# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



Schematic diagram



Mounting

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



## Classifications

### ETIM

ETIM 8.0

EC001478

### UNSPSC

UNSPSC 21.0

43222600

# TC ROUTER 2002T-4G - Router

2702530

<https://www.phoenixcontact.com/us/products/2702530>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)